



Mitutoyo



**PRODUCT DESCRIPTION**

- » Convenient set of internal micrometres
- » Includes ring gauge(s) and an extension piece

**SCOPE OF DELIVERY**

- » Certificate of inspection and a wooden box

Set contents	MB <sup>1)</sup>	No.	EUR
<ul style="list-style-type: none"> <li>» Analogue internal micrometre MIA 10232/ 6- 8</li> <li>» Analogue internal micrometre MIA 10232/ 8-10</li> <li>» Analogue internal micrometre MIA 10232/10-12</li> <li>» Ring gauge MFL 2250/ 8</li> <li>» Ring gauge MFL 2250/10</li> <li>» Extension piece</li> </ul>	6- 12	MIA 12232/ 6- 12	<>
<ul style="list-style-type: none"> <li>» Ring gauge MFL 2250/16</li> <li>» Analogue internal micrometre MIA 10232/12-16</li> <li>» Analogue internal micrometre MIA 10232/16-20</li> <li>» Extension piece</li> </ul>	12- 20	MIA 12232/12- 20	<>
<ul style="list-style-type: none"> <li>» Ring gauge MFL 2250/25</li> <li>» Ring gauge MFL 2250/40</li> <li>» Analogue internal micrometre MIA 10232/20-25</li> <li>» Analogue internal micrometre MIA 10232/25-30</li> <li>» Analogue internal micrometre MIA 10232/30-40</li> <li>» Analogue internal micrometre MIA 10232/40-50</li> <li>» Extension piece</li> </ul>	20- 50	MIA 12232/20- 50	<>
<ul style="list-style-type: none"> <li>» Ring gauge MFL 2250/62</li> <li>» Ring gauge MFL 2250/87</li> <li>» Analogue internal micrometre MIA 10232/50- 63</li> <li>» Analogue internal micrometre MIA 10232/62- 75</li> <li>» Analogue internal micrometre MIA 10232/75- 88</li> <li>» Analogue internal micrometre MIA 10232/87-100</li> <li>» Extension piece</li> </ul>	50-100	MIA 12232/50-100	<>

1) MB: measuring range

Pre-calibrated on request