



PRODUCT DESCRIPTION

- » Reduced wear through ball bearing with floating support
- » Easy and precise handling through pencil-shaped design
- » Optimal for diamond mounted points and rotary burrs

APPLICATION

- » Do not use with lubricated air!

INCLUDED IN THE DELIVERY

- » Hoses, Ø3 mm collet and clamping equipment

Wt.	d1	Q	Output	p	l	ls ¹⁾	n max.	No.	EUR
270 g	3	210 l/min	70 W	6 bar	173	1.5 m	65,000 min ⁻¹	GDST 2000/65	< >

1) ls: hose length

i Spare parts and repair by request