

AIR TURBINE GRINDER, PREMIUM

GDST 2200





PRODUCT DESCRIPTION

- » High-speed grinder
- >> Reduced wear through ball bearing with floating support
- >> Compact, ergonomic design
- >> Optimal for tools with a tool head diameter of up to 6 mm

APPLICATION

» Do not use with lubricated air!

INCLUDED IN THE DELIVERY

» Hoses, Ø3 mm collet and clamping equipment

Wt.	d1	Q	Output	р	I	ls ¹⁾	n max.	No.	EUR
270 g	3	320 l/min	100 W	6 bar	135	1.5 m	100,000 min ⁻¹	GDST 2200/100	<>

1) ls: hose length



Spare parts and repair by request