

EVO

PRODUCT DESCRIPTION

- » Ergonomically shaped polisher attachment
- » Adjustable axial angle
- » Low-vibration thanks to the integrated damper
- » Infinitely variable stroke length

INCLUDED IN THE DELIVERY

- » Clamping and servicing equipment

Wt.	n	lk ¹⁾	d1	Motor	Stroke	No.	EUR
800 g	0 - 7600 min ⁻¹	1.5 m	3	integrated	0 - 6,0 mm	GESM 2610/0-6,0	< >

1) lk: cable length

i Spare parts and repair by request

