


MATERIAL

» 2.0060 (E-Cu 57)



b1	l1	H	Nr.	EUR
20	60	30	V 91554/20/ 60/30	< >
20	60	50	V 91554/20/ 60/50	< >
20	80	30	V 91554/20/ 80/30	< >
20	80	50	V 91554/20/ 80/50	< >
20	100	30	V 91554/20/100/30	< >
20	100	50	V 91554/20/100/50	< >
25	60	30	V 91554/25/ 60/30	< >
25	60	50	V 91554/25/ 60/50	< >
25	80	30	V 91554/25/ 80/30	< >
25	80	50	V 91554/25/ 80/50	< >
25	100	30	V 91554/25/100/30	< >
25	100	50	V 91554/25/100/50	< >

b1	l1	H	Nr.	EUR
30	60	30	V 91554/30/ 60/30	< >
30	60	50	V 91554/30/ 60/50	< >
30	80	30	V 91554/30/ 80/30	< >
30	80	50	V 91554/30/ 80/50	< >
30	100	30	V 91554/30/100/30	< >
30	100	50	V 91554/30/100/50	< >
40	60	30	V 91554/40/ 60/30	< >
40	60	50	V 91554/40/ 60/50	< >
60	60	30	V 91554/60/ 60/30	< >
60	60	50	V 91554/60/ 60/50	< >
70	70	30	V 91554/70/ 70/30	< >
70	70	50	V 91554/70/ 70/50	< >