

PRODUCT DESCRIPTION

Versatile high-performance grease for injection tools with highest demands. Ideal for lubricating ejectors, slides and pillar guides as well as all moving and sliding die and mould components.

ADVANTAGES

- » Usable up to 180°C (temporarily 200°C)
- » Long-term lubrication
- » High corrosion and wear protection
- » Excellent texture and temperature behaviour

APPLICATION

Clean designated area thoroughly and apply grease thinly.

Package	Content	No.	EUR
Dispenser	180g	VGS 180/ 180	< >
Can	900g	VGS 180/ 900	< >

 Material safety data sheets at each product under www.meusburger.com



CHARACTERISTICS

VGS 180	Value	Test procedure
Colour	beige	DIN ISO 2049
Maximum temperature	180 °C	
Drop point	≥ 240 °C	DIN ISO 2176
NLGI-class	1-2	DIN 51818
Worked penetration	285-315 1/10mm	DIN ISO 2137
Base oil	polyalphaolefin	
Thickener	polyurea	
Density	0.92 g/cm ³	DIN 51 757