

PRODUCT DESCRIPTION

- » Powerful: light output is 100 W
- » Infinitely variable light intensity



Power supply	Wt.	Colour temperature	Output	No.	EUR
230V/50Hz	3.8 kg	3100 K	100 W	BAL 4232/100	< >