

HIGH-PERFORMANCE TECHNICAL GREASE USABLE UP TO 180°C

VGM 160

PRODUCT DESCRIPTION

High-performance grease for universal application in injection moulds and stamping dies. Ideal for lubricating moving and sliding components and for servicing machines and facilities.

ADVANTAGES

- >> Long-term lubrication
- >> High corrosion and wear protection
- >> Excellent texture and temperature behaviour
- >> 100% water-resistant

APPLICATION

Clean designated area thoroughly and apply grease thinly.

Package	Content	No.	EUR
Dispenser	180g	VGM 160/ 180	<>
Can	900g	VGM 160/ 900	<>



CHARACTERISTICS

VGM 160	Value	Test procedure
Colour	light brown	DIN ISO 2049
Maximum temperature	180 °C	
Drop point	≥ 240 °C	DIN ISO 2176
NLGI-class	1-2	DIN 51818
Worked penetration	290-310 1/10mm	DIN ISO 2137
Base oil	mineral oil	
Thickener	polyurea	
Density	0.96 g/cm ³	DIN 51 757

