

PRODUCT DESCRIPTION

- » Ultrasonic material thickness gauge
- » External measuring head
- » Internal data memory

APPLICATION

- » Selectable units: mm, inch
- » Scan mode (10 measurements per second) or single measuring point selectable



d ¹⁾	f ²⁾	Tol.	MB ³⁾	Readability	No.	EUR
6 mm	7 MHz	5%	0,75-80	0.1	MUM 1210/ 80/ 0,1	< >
6 mm	7 MHz	5%	0,75-80	0.01	MUM 1210/ 80/0,01	< >

1) Measuring head diameter

2) Measuring frequency

3) MB: measuring range