meusburger

DIGITAL CALLIPER AOS

PRODUCT DESCRIPTION

- » Ultimate precision through Absolute Measuring System
- » Reliable measuring even with a slightly wet guiding surface
- >> With locking screw
- >> Battery life: approx. 18,000 hours

INCLUDED IN THE DELIVERY

» Certificate of inspection, a battery (SR44) and a plastic case

MB ¹⁾	TM ²⁾	PU PCS. / PU	No.
0-150	flat	2	MSD 10002/150/F/Set2
MB: measuring range	2) TM: de	opth bar	

1) N

Pre-calibrated on request

DIGITAL CALLIPER IP67

PRODUCT DESCRIPTION

- >> Ultimate precision through Absolute Measuring System
- >> With locking screw
- » Battery life: approx. 20,000 hours
- » Ideal for use in machining situations that include splashing coolant fluid

INCLUDED IN THE DELIVERY

» Certificate of inspection, a battery (SR44) and a plastic case

MB ¹⁾	TM ²⁾	PU Pcs. / PU	No.
0-150	flat	2	MSD 20002/150/F/Set2
10	0) THE		

1) MB: measuring range

2) TM: depth bar

Pre-calibrated on request

ANALOGUE VERNIER CALLIPER

PRODUCT DESCRIPTION

- >> From hardened steel
- » Main scale and vernier scale with satin chrome finish
- >> With locking screw

INCLUDED IN THE DELIVERY

>> A plastic case

MB ¹⁾	TM ²	PU PCS. / PU	No.
0-150	flat	3	MSA 10002/150/F/Set3
1) MB: measuring range	2) TM: de	pth bar	

Pre-calibrated on request



NOW





MSD 10002

MSA 10002

meusburger

ANALOGUE EXTERNAL MICROMETRE

PRODUCT DESCRIPTION

- » Suited for one-handed operation
- » For more precise measuring results even for the inexpert user
- » Ratchet on the fast drive mechanism and the thimble

INCLUDED IN THE DELIVERY

» Certificate of inspection, setting gauge (only for 25-50 mm) and a plastic case

MB ⁽⁾	PU Pcs. / PU	No.
0- 25	2	MBA 12002/ 0-25/Set-2

1) MB: measuring range

Pre-calibrated on request

DIGITAL EXTERNAL MICROMETRE IP65

PRODUCT DESCRIPTION


- » Can be adjusted easily and to high precision
- » Ratchet on the fast drive mechanism
- » Ideal for use in machining situations that include splashing coolant fluid

INCLUDED IN THE DELIVERY

» Certificate of inspection (0-25 mm and 25-50 mm only), setting gauge (from 25-50 mm), a battery (SR44) and a plastic case

MB ¹⁾	PU PU Pcs. / PU	No.
0- 25	2	MBD 50002/ 0- 25/Set-2

1) MB: measuring range



DIGITAL EXTERNAL MICROMETRE QUANTUMIKE IP65

PRODUCT DESCRIPTION

- » Ideal for use in machining situations that include splashing coolant fluid
- » Ratchet on the fast drive mechanism and the thimble
- » Feed is 4 times faster through 2 mm spindle pitch

INCLUDED IN THE DELIVERY

» Certificate of inspection (0-25 mm and 25-50 mm only), setting gauge (from 25-50 mm), a battery (SR44) and a plastic case

MB ¹⁾	PU Pcs. / PU	No.
0- 25	2	MBD 50022/ 0- 25/Set-2
1) MB: measuring range		

MBD 50022

Pre-calibrated on request



MBA 12002

meusburger

DIGITAL DIAL INDICATOR, 0.01 MM

PRODUCT DESCRIPTION

- >> Ultimate precision through Absolute Measuring System
- » Only 40 LUX required for solar operation
- » No battery replacement required

INCLUDED IN THE DELIVERY

» Certificate of inspection

MB ¹⁾	PU Pcs. / PU	No.
12,7	2	MUD 12022/12,7/Set-2

1) MB: measuring range

Pre-calibrated on request

ANALOGUE DIAL INDICATOR

PRODUCT DESCRIPTION

- » Rotatable bezel with adjustable tolerance markers
- $\boldsymbol{\boldsymbol{\succ}}$ Enables optimal inspection or adjustment of a workpiece

INCLUDED IN THE DELIVERY

» Certificate of inspection

certificate of hispection		
MB ¹⁾	PU Pcs. / PU	No.
10	2	MUA 10202/10/Set-2

1) MB: measuring range

Pre-calibrated on request





MUD 12022