


DESCRIZIONE DEL PRODOTTO

» Secondo DIN 580

MATERIALE

» C15E



l1	l2	d2	d3	d4	d1	WLL max. kg	 max. kg	N°	EUR
13	18	36	20	20	M 8	140	100	E 1270/ 8	<>
17	22,5	45	25	25	M10	230	170	E 1270/10	<>
20	26	54	30	30	M12	340	240	E 1270/12	<>
27	30,5	63	35	35	M16	700	500	E 1270/16	<>
30	35	72	40	40	M20	1.200	860	E 1270/20	<>
36	45	90	50	50	M24	1.800	1.290	E 1270/24	<>
45	55	108	65	60	M30	3.200	2.300	E 1270/30	<>
54	65	126	75	70	M36	4.600	3.300	E 1270/36	<>
63	136,5	144	85	80	M42	6.300	4.500	E 1270/42	<>
68	152	166	100	90	M48	8.600	6.100	E 1270/48	<>