

WHITE ASSEMBLY PASTE

VAP 1000



PRODUCT DESCRIPTION

All-purpose paste for mounting highly stressed screw and plug connections and for lubricating extremely stressed gliding points. Protects against fitting and fretting corrosion. Loosens tight screws and sprues after long idle state.

ADVANTAGES

- >> Usable up to 1400°C
- » Contains neither toxic nor metallic substances
- >> White coloured solid lubricants
- >> Extremely pressure resistant
- >>> Resistant to hot water, acids and alkali
- >> H1 registered

APPLICATION

Apply paste evenly.

Containers	Content	No.	EUR
Dispenser	250g	VAP 1000/250	<>
Can	750g	VAP 1000/750	<>



CHARACTERISTICS

VAP 1000	Value	Test procedure
Colour	white	DIN ISO 2049
Maximum temperature	1400 °C	
Drop point	none	DIN ISO 2176
NLGI-class	1	DIN 51818
Worked penetration	310-340 1/10mm	DIN ISO 2137
Base oil	mineral oil	
Thickener	gel	
Density	1.4 g/cm ³	DIN 51 757



