

PRODUCT DESCRIPTION

- » Hardness comparison plates for Shore A or Shore D
- » Tolerance up to ± 2 HD
- » Suitable for Shore hardness tester models MHM 1111 and MHM 1211



Tol.	n ¹⁾	Hardness type	No.	EUR
+/-2	3	Shore D	MHMZ 1110/3/D	< >
+/-2	7	Shore A	MHMZ 1110/7/A	< >

1) n: Number of test plates