

### PRODUCT DESCRIPTION

- » Low effort and high cutting performance through optimal force transmission
- » Polished surface with satin chrome finish

### MATERIAL

- » Forged chrome vanadium high-performance steel with induction hardened precision cutting edges (64 HRC)



l	No.	EUR
160	V 20410/160	< >
180	V 20410/180	< >
200	V 20410/200	< >