




PRODUKTBESCHREIBUNG

- » Verschiedenste Formen für alle Einsatzzwecke
- » Passend für alle Messuhren



Form	M	w	l	d	Ausführung	Nr.	EUR
	2,5	-	5,8	3,1	Stahl	MUZ 4005/01/3,1-S	<>
	2,5	-	5,8	2,4	Stahl	MUZ 4005/01/2,4-S	<>
	2,5	-	5,8	3,1	Hartmetall	MUZ 4005/01/3,1-H	<>
	2,5	-	5,8	3,1	Rubin	MUZ 4005/01/3,1-R	<>
	2,5	-	5,8	3,1	Kunststoff	MUZ 4005/01/3,1-K	<>
	2,5	-	16	3,1	Stahl	MUZ 4005/01/16-S	<>
	2,5	-	6	4,8	Stahl	MUZ 4005/02/4,8/ 6-S	<>
	2,5	-	11	1,5	Stahl	MUZ 4005/02/1,5/11-S	<>
	2,5	-	30	1,5	Stahl	MUZ 4005/02/1,5/30-S	<>
	2,5	-	-	10	Stahl	MUZ 4005/03/10-S	<>
	2,5	-	-	20	Stahl	MUZ 4005/03/20-S	<>
	2,5	-	-	30	Stahl	MUZ 4005/03/30-S	<>
	2,5	60	4	4,5	Stahl	MUZ 4005/04/60-S	<>
	2,5	15	10	3,5	Stahl	MUZ 4005/05/10-S	<>
	2,5	-	12	1	Stahl	MUZ 4005/06/ 1-S	<>
	2,5	-	12	2	Stahl	MUZ 4005/06/ 2-S	<>
	2,5	-	12	3	Stahl	MUZ 4005/06/ 3-S	<>
	2,5	-	12	4	Stahl	MUZ 4005/06/ 4-S	<>
	2,5	-	12	5	Stahl	MUZ 4005/06/ 5-S	<>
	2,5	-	12	6	Stahl	MUZ 4005/06/ 6-S	<>
	2,5	-	18	7	Stahl	MUZ 4005/06/ 7-S	<>
	2,5	-	18	10	Stahl	MUZ 4005/06/10-S	<>
	2,5	-	16	-	Stahl	MUZ 4005/07/16-S	<>
	2,5	-	-	10	Stahl	MUZ 4005/08/10-S	<>

	Form	M	w	l	d	Ausführung	Nr.	EUR
25		2,5	90	-	2	Stahl	MUZ 4005/25/90	< >
30		2,5	109	-	2	Stahl	MUZ 4005/30/109	< >
40		2,5	-	9	M1.6	Stahl	MUZ 4005/40/1,6	< >