


### MATERIAL

» Graphite Q70, Q60, Q40



h2	H	b2/l2	b1	l1	h1	Q70	EUR	Q60	EUR	Q40	EUR
32	62	15	15	15	30		-	V 92574/15/15 15/30	<>	V 92577/15/15 15/30	<>
32	82	15	15	15	50		-	V 92574/15/15 15/50	<>	V 92577/15/15 15/50	<>
32	112	15	15	15	80		-	V 92574/15/15 15/80	<>	V 92577/15/15 15/80	<>
32	62	15	20	20	30		-	V 92574/15/20 20/30	<>	V 92577/15/20 20/30	<>
32	82	15	20	20	50	V 92571/15/20 20/50	<>	V 92574/15/20 20/50	<>	V 92577/15/20 20/50	<>
32	112	15	20	20	80	V 92571/15/20 20/80	<>	V 92574/15/20 20/80	<>	V 92577/15/20 20/80	<>
32	62	15	25	25	30		-	V 92574/15/25 25/30	<>	V 92577/15/25 25/30	<>
32	82	15	25	25	50		-	V 92574/15/25 25/50	<>	V 92577/15/25 25/50	<>
32	112	15	25	25	80	V 92571/15/25 25/80	<>		-		-
32	62	15	30	30	30		-	V 92574/15/30 30/30	<>		-
32	82	15	30	30	50	V 92571/15/30 30/50	<>	V 92574/15/30 30/50	<>	V 92577/15/30 30/50	<>
32	112	15	30	30	80		-		-	V 92577/15/30 30/80	<>
32	62	15	35	35	30		-	V 92574/15/35 35/30	<>		-
32	82	15	35	35	50	V 92571/15/35 35/50	<>	V 92574/15/35 35/50	<>		-
32	62	15	40	40	30		-	V 92574/15/40 40/30	<>	V 92577/15/40 40/30	<>
32	82	15	40	40	50	V 92571/15/40 40/50	<>	V 92574/15/40 40/50	<>	V 92577/15/40 40/50	<>
32	112	15	40	40	80	V 92571/15/40 40/80	<>	V 92574/15/40 40/80	<>	V 92577/15/40 40/80	<>
40	72	25	25	25	32		-	V 92574/25/25 25/32	<>	V 92577/25/25 25/32	<>
40	102	25	25	25	62		-	V 92574/25/25 25/62	<>	V 92577/25/25 25/62	<>
40	120	25	25	25	80		-	V 92574/25/25 25/80	<>	V 92577/25/25 25/80	<>
40	72	25	30	30	32	V 92571/25/30 30/32	<>	V 92574/25/30 30/32	<>	V 92577/25/30 30/32	<>
40	92	25	30	30	52	V 92571/25/30 30/52	<>	V 92574/25/30 30/52	<>	V 92577/25/30 30/52	<>
40	120	25	30	30	80		-	V 92574/25/30 30/80	<>		-
40	72	25	35	35	32		-	V 92574/25/35 35/32	<>		-
40	92	25	35	35	52	V 92571/25/35 35/52	<>	V 92574/25/35 35/52	<>		-
40	120	25	35	35	80	V 92571/25/35 35/80	<>	V 92574/25/35 35/80	<>		-
40	72	25	40	40	32	V 92571/25/40 40/32	<>	V 92574/25/40 40/32	<>		-
40	92	25	40	40	52	V 92571/25/40 40/52	<>	V 92574/25/40 40/52	<>	V 92577/25/40 40/52	<>
40	120	25	40	40	80	V 92571/25/40 40/80	<>	V 92574/25/40 40/80	<>		-
40	92	25	50	50	52	V 92571/25/50 50/52	<>	V 92574/25/50 50/52	<>	V 92577/25/50 50/52	<>
40	120	25	50	50	80	V 92571/25/50 50/80	<>	V 92574/25/50 50/80	<>		-