# meusburger

# M-LINE MICRO MOTOR HANDPIECE, TORQUE

#### **PRODUCT DESCRIPTION**

- » Extremely high-torque, speed-reduced motor, perfect for coarse finishing and large tools
- » Highest clamping force due to simple key clamping system for shank diameter Ø6 mm
- » Smooth operation and highest stability
- » Ergonomic aluminium housing with built-in front fan against dirt and dust
- $\boldsymbol{\boldsymbol{\succ}}$  Integrated motor cooling for longest switch-on and service life
- $\boldsymbol{\boldsymbol{\succ}}$  Illuminated on/off switch conveniently located on the handpiece

## INCLUDED IN THE DELIVERY

- » Collet (GESM 20125) with slotted spring pin
- » Collet holder (GESM 20126) and double open ended spanner (GESM 20127)
- » Motor cable

Wt.	<b>Ik</b> <sup>1)</sup>	Output	n	d1	No.	EUR
416 g	1.85 m	260 W	1,000 - 30,000 min <sup>-1</sup>	6	GESM 2011/260/30/ 6	< >
4) 11 1 1 1						

1) lk: cable length

i Spare parts and repair by request

### CHARACTERISTICS

GESM 2011	Value
Motor type	Brushless DC motor
Torque	11.6 Ncm
Concentricity	< 0,02 mm



## **GESM 2011**