




PRODUCT DESCRIPTION

» For chamfering and deburring workpiece edges

MATERIAL

» Carbide, TiAlN multi-layer coated

Z	l	l1	d	No.	EUR
4	57	3	6	WZF 15236/ 6	< >
4	63	4	8	WZF 15236/ 8	< >
4	72	5	10	WZF 15236/10	< >
4	83	6	12	WZF 15236/12	< >



REFERENCE VALUES FOR CHAMFERING

WZF 15234 WZF 15236 WZF 15238	Material	Strength	Vc ¹ m/min.	d					
				4	6	8	10	12	16
				fz ² (mm/z)					
	1.1730	640 N/mm ²	120	0.040	0.050	0.065	0.070	0.080	0.100
	1.2083	780 N/mm ²	100	0.040	0.050	0.065	0.070	0.080	0.085
	1.2085	1080 N/mm ²	100	0.038	0.048	0.060	0.065	0.075	0.080
	1.2162	660 N/mm ²	120	0.040	0.050	0.065	0.070	0.080	0.100
	1.2311	1080 N/mm ²	100	0.038	0.048	0.060	0.065	0.075	0.088
	1.2312	1080 N/mm ²	100	0.038	0.048	0.060	0.065	0.075	0.088
	1.2316	1010 N/mm ²	100	0.038	0.048	0.060	0.065	0.075	0.080
	1.2343	780 N/mm ²	120	0.040	0.050	0.065	0.070	0.080	0.100
	1.2379	780 N/mm ²	100	0.040	0.050	0.065	0.070	0.080	0.085
	1.2714HH	1350 N/mm ²	90	0.038	0.048	0.060	0.065	0.075	0.080
	1.2767	830 N/mm ²	120	0.040	0.050	0.065	0.070	0.080	0.088
	1.2842	775 N/mm ²	120	0.040	0.050	0.065	0.070	0.080	0.088
	Steel	1400 N/mm ²	90	0.038	0.048	0.060	0.065	0.075	0.080



ap ≈ 0.5 x d

1) Vc: cutting speed (m/min.)

2) fz: feed per cut (mm per tooth)



You can find further materials and cutting values in the cutting data calculator.