

M-LINE MICRO MOTOR HANDPIECE, COLLET

GESM 2012

PRODUCT DESCRIPTION

- >> Fast and high-torque motor, perfect for machining high-strength materials
- » Highest clamping force due to simple key clamping system for shank diameters up to Ø6 mm
- >>> Smooth operation even at highest speeds
- >> Ergonomic aluminium housing with built-in front fan against dirt and dust
- » Integrated motor cooling for longest switch-on and service life
- >> Illuminated on/off switch conveniently located on the handpiece

INCLUDED IN THE DELIVERY

- >> Collet (GESM 20125) with slotted spring pin
- » Collet holder (GESM 20126) and double open ended spanner (GESM 20127)
- >> Motor cable

Wt.	lk ¹⁾	Output	n	d1	No.	EUR
414 g	1.85 m	260 W	1,000 - 60,000 min ⁻¹	3	GESM 2012/260/60/ 3	<>
416 g	1.85 m	260 W	1,000 - 60,000 min ⁻¹	6	GESM 2012/260/60/ 6	<>

1) lk: cable length



Spare parts and repair by request

CHARACTERISTICS

GESM 2012	Value
Motor type	Brushless DC motor
Torque	8.9 Ncm
Concentricity	< 0,02 mm