

according to UK REACH Regulation

Page 1 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

VGI 260

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### Use of the substance/mixture

Lubricants, greases, release products

#### Uses advised against

Any non-intended use.

## 1.3. Details of the supplier of the safety data sheet

Company name: Meusburger Georg GmbH & Co KG

Street: Kesselstrasse 42
Place: A-6960 Wolfurt

Telephone: +43 5574 6706-0 Telefax: +43 5574 6706-12

e-mail: office@meusburger.com Internet: www.meusburger.com

Responsible Department: Dr. Gans-Eichler e-mail: info@tge-consult.de

Chemieberatung GmbH Tel.: +49 2534 41594-0 Otto-Hahn-Str. 36 www.tge-consult.de

D-48161 Muenster

1.4. Emergency telephone Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240

number:

### **Further Information**

Safety Data Sheet according to UK-REACH Regulation

# **SECTION 2: Hazards identification**

## 2.1. Classification of the substance or mixture

### **GB CLP Regulation**

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

#### 2.2. Label elements

# **GB CLP Regulation**

# Special labelling of certain mixtures

EUH210 Safety data sheet available on request.

## Additional advice on labelling

Labelling according to GHS (GB CLP) regulation.: none

# 2.3. Other hazards

The substances in the mixture (> 0.1%) do not meet the PBT/vPvB criteria according to UK REACH.

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

No risks worthy of mention. Please observe the information on the safety data sheet at all times.

## SECTION 3: Composition/information on ingredients

## 3.2. Mixtures

### **Hazardous components**



Print date: 13.03.2023

according to UK REACH Regulation

Page 2 of 11

Revision date: 02.03.2023

VGI 260

CAS No	Chemical name	Quantity
EC No	GHS Classification	
REACH No		
Index No		
9002-84-0	Polytetrafluoroethylene	25 - 50 %
618-337-2		
17265-14-4	Disodium sebacate	0,5 - 2,5 %
241-300-3	Eye Irrit. 2; H319	
01-2120762063-61		

Full text of H and EUH statements: see section 16.

### Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity		
	Specific Conc. L	onc. Limits, M-factors and ATE			
17265-14-4	241-300-3	Disodium sebacate	0,5 - 2,5 %		
dermal: LD50 = > 2000 mg/kg; oral: LD50 = > 5000 mg/kg					

## **Further Information**

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

## **SECTION 4: First aid measures**

### 4.1. Description of first aid measures

### **General information**

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

# After inhalation

Paste: Inhalation is unlikely because of the low vapour pressure of the substance at ambient temperature. In case of respiratory tract irritation, consult a physician.

#### After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

## After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an ophthalmologist.

## After ingestion

Rinse mouth thoroughly with water. Let water be drunken in little sips (dilution effect). Do NOT induce vomiting. In all cases of doubt, or when symptoms persist, seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

No information available.

## 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.



according to UK REACH Regulation

Page 3 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

# **SECTION 5: Firefighting measures**

# 5.1. Extinguishing media

### Suitable extinguishing media

The product itself does not burn. Co-ordinate fire-fighting measures to the fire surroundings.

#### Unsuitable extinguishing media

High power water jet.

#### 5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide Carbon dioxide (CO2).

### 5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

### **Additional information**

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.

Co-ordinate fire-fighting measures to the fire surroundings.

### SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

## General advice

Avoid dust formation.

Do not breathe dust.

Special danger of slipping by leaking/spilling product.

#### For non-emergency personnel

Wear personal protection equipment (refer to section 8).

### For emergency responders

No special measures are necessary.

### 6.2. Environmental precautions

Discharge into the environment must be avoided.

### 6.3. Methods and material for containment and cleaning up

# For containment

Take up mechanically.

Treat the recovered material as prescribed in the section on waste disposal.

### For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

## 6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

## SECTION 7: Handling and storage

# 7.1. Precautions for safe handling

### Advice on safe handling

Wear personal protection equipment (refer to section 8).

### Advice on protection against fire and explosion

Usual measures for fire prevention. Dust clouds may present an explosion hazard.



according to UK REACH Regulation

Page 4 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

### Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

#### Further information on handling

Avoid generation of dust.

General protection and hygiene measures: refer to chapter 8

## 7.2. Conditions for safe storage, including any incompatibilities

## Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

#### Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

## Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorbtion of humidity.

Recommended storage temperature: 20 °C

Protect against: frost. UV-radiation/sunlight. heat. Humidity

## 7.3. Specific end use(s)

See section 1.

# SECTION 8: Exposure controls/personal protection

# 8.1. Control parameters

### **DNEL/DMEL values**

CAS No	Substance				
DNEL type		Exposure route	Effect	Value	
17265-14-4 Disodium sebacate					
Worker DNEL, long-term inhalation systemic 35,26 mg/m³				35,26 mg/m³	
Worker DNEL,	long-term	dermal	systemic	10 mg/kg bw/day	
Consumer DNEL, long-term		inhalation	systemic	8,7 mg/m³	
Consumer DNEL, long-term		dermal	systemic	5 mg/kg bw/day	
Consumer DNEL, long-term		oral	systemic	5 mg/kg bw/day	

## **PNEC values**

CAS No	AS No Substance			
Environmental compartment Value				
17265-14-4	Disodium sebacate			
Freshwater 0,018 mg/l				
Freshwater (intermittent releases) 0,18 mg/l				
Marine water 0,				
Freshwater sediment		0,548 mg/kg		
Marine sediment		0,055 mg/kg		
Micro-organisms in sewage treatment plants (STP)		10 mg/l		
Soil	0,099 mg/kg			



according to UK REACH Regulation

Page 5 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

**VGI 260** 

### Additional advice on limit values

To date, no national critical limit values exist.

### 8.2. Exposure controls

## Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

Dust should be exhausted directly at the point of origin.

#### Individual protection measures, such as personal protective equipment

#### Eve/face protection

Dust protection goggles.

### Hand protection

In case of prolonged or frequently repeated skin contact:

Wear suitable gloves.

Suitable material:

NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm

Breakthrough time >= 8 h

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Before using check leak tightness / impermeability. In the case of wanting to use the gloves again, clean them before taking off and air them well.

### Skin protection

Suitable protective clothing: Protective clothing.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500 (D).

## Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required.

Respiratory protection necessary at:

- -Exceeding exposure limit values
- -Insufficient ventilation and Generation/formation of dust

Suitable respiratory protective equipment: particulates filter device (DIN EN 143). Type: P1-3

The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

### Thermal hazards

Material handled at elevated temperature may cause thermal burns by contact with molten product.

#### **Environmental exposure controls**

No special precautionary measures are necessary.

### SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state: Paste
Colour: whitish
Odour: neutral
Odour threshold: not determined

Melting point/freezing point:

Boiling point or initial boiling point and

not determined

boiling range:



according to UK REACH Regulation Page 6 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

Flammability: not determined Lower explosion limits: not relevant Upper explosion limits: not relevant Flash point: not relevant Auto-ignition temperature: not relevant Decomposition temperature: > 290 °C pH-Value: not determined Viscosity / kinematic: not relevant Water solubility: insoluble

Solubility in other solvents

insoluble in: Hydrocarbons, Alcohol

Dissolution rate: not relevant Partition coefficient n-octanol/water: SECTION 12: Ecological information Dispersion stability: not relevant Vapour pressure: not determined Density (at 20 °C): 1,948 g/cm<sup>3</sup> Bulk density: not determined Relative vapour density: not relevant Particle characteristics: not determined

### 9.2. Other information

# Information with regard to physical hazard classes

Explosive properties

Dust clouds may present an explosion hazard.

Sustaining combustion: Not sustaining combustion

Self-ignition temperature

Solid: not determined
Gas: not relevant

Oxidizing properties

none

### Other safety characteristics

not applicable Evaporation rate: Solvent separation test: not applicable Solvent content: not determined Solid content: not determined Sublimation point: not determined Softening point: not determined Pour point: not determined Viscosity / dynamic: not determined Flow time: not applicable

**Further Information**No information available.

## SECTION 10: Stability and reactivity

# 10.1. Reactivity

No information available.

## 10.2. Chemical stability



according to UK REACH Regulation

Page 7 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

The product is chemically stable under recommended conditions of storage, use and temperature.

### 10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.

Refer to chapter 10.5.

#### 10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat.

### 10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong. Strong acid.

#### 10.6. Hazardous decomposition products

Carbon monoxide (CO). Carbon dioxide (CO2). Gas/vapours, toxic. Pyrolysis products, toxic, contains fluorine.

## **SECTION 11: Toxicological information**

## 11.1. Information on hazard classes as defined in GB CLP Regulation

## Toxicocinetics, metabolism and distribution

No data available.

### **Acute toxicity**

Based on available data, the classification criteria are not met.

CAS No	Chemical name					
	Exposure route	Dose		Species	Source	Method
17265-14-4	Disodium sebacate					
	oral	LD50 mg/kg	> 5000	Rat	ECHA dossier	OECD 401
	dermal	LD50 mg/kg	> 2000	Rat	ECHA dossier	OECD 402

### Irritation and corrosivity

Based on available data, the classification criteria are not met.

### Sensitising effects

Based on available data, the classification criteria are not met.

# Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

## STOT-single exposure

Based on available data, the classification criteria are not met.

## STOT-repeated exposure

Based on available data, the classification criteria are not met.

### **Aspiration hazard**

Based on available data, the classification criteria are not met.

## Specific effects in experiment on an animal

No data available.

## 11.2. Information on other hazards

### **Endocrine disrupting properties**

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.



according to UK REACH Regulation

Page 8 of 11

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

#### Other information

No data available.

# **SECTION 12: Ecological information**

### 12.1. Toxicity

The product has not been tested.

CAS No	Chemical name						
	Aquatic toxicity	Dose		[h]   [d]	Species	Source	Method
17265-14-4	Disodium sebacate	Disodium sebacate					
	Acute fish toxicity	LC50 mg/l	> 100	96 h	Danio rerio	ECHA dossier	OECD 203
	Acute algae toxicity	ErC50 mg/l	38,7		Skeletonema costatum	ECHA dossier	ISO 10253
	Acute crustacea toxicity	EC50 mg/l	> 100	48 h	Daphnia magna	ECHA dossier	OECD 202

### 12.2. Persistence and degradability

The product has not been tested

THE PI	oddot has not been tested.					
CAS No	Chemical name					
	Method	Value	d	Source		
	Evaluation					
17265-14-4	Disodium sebacate					
	OECD 306	89%	28	ECHA dossier		
	Readily biodegradable (according to OECD criteria).					

## 12.3. Bioaccumulative potential

## Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
17265-14-4	Disodium sebacate	-4,9

## 12.4. Mobility in soil

No data available.

### 12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %

## 12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1

## 12.7. Other adverse effects

No data available.

## **Further information**

Do not allow to enter into surface water or drains.



Page 9 of 11

## Safety Data Sheet

according to UK REACH Regulation

Print date: 13.03.2023 Revision date: 02.03.2023

VGI 260

## **SECTION 13: Disposal considerations**

#### 13.1. Waste treatment methods

#### **Disposal recommendations**

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal. Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process. Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

#### List of Wastes Code - residues/unused products

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused

products; organic wastes other than those mentioned in 16 03 05

### List of Wastes Code - used product

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused

products; organic wastes other than those mentioned in 16 03 05

#### List of Wastes Code - contaminated packaging

150106 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND

PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately

collected municipal packaging waste); mixed packaging

## Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

## SECTION 14: Transport information

	4			/DID
∟and	transi	port (	AUK	/KIU)

**14.1. UN number or ID number:** No dangerous good in sense of this transport regulation.

**14.2. UN proper shipping name:**No dangerous good in sense of this transport regulation. **14.3. Transport hazard class(es):**No dangerous good in sense of this transport regulation.

**14.4. Packing group:**No dangerous good in sense of this transport regulation.

Inland waterways transport (ADN)

**14.1. UN number or ID number:** No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:14.3. Transport hazard class(es):No dangerous good in sense of this transport regulation.No dangerous good in sense of this transport regulation.

**14.4. Packing group:**No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

**14.1. UN number or ID number:** No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

No dangerous good in sense of this transport regulation.

14.4. Packing group: No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number or ID number: No dangerous good in sense of this transport regulation.

**14.2. UN proper shipping name:** No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):14.4. Packing group:No dangerous good in sense of this transport regulation.No dangerous good in sense of this transport regulation.

14.4. Packing group:
14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No



Print date: 13.03.2023

according to UK REACH Regulation

Page 10 of 11

Revision date: 02.03.2023

VGI 260

### 14.6. Special precautions for user

Refer to section 6 - 8

### 14.7. Maritime transport in bulk according to IMO instruments

not relevant

## **SECTION 15: Regulatory information**

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **EU** regulatory information

2010/75/EU (VOC): not determined 2004/42/EC (VOC): not determined

Information according to 2012/18/EU Not subject to 2012/18/EU (SEVESO III)

(SEVESO III):

#### **Additional information**

Safety Data Sheet according to UK-REACH Regulation

This mixture is classified as not hazardous according to GHS (GB CLP).

UK REACH Appendix XVII, No (mixture): not relevant

### National regulatory information

Water hazard class (D): 1 - slightly hazardous to water

### 15.2. Chemical safety assessment

For the following substances of this mixture a chemical safety assessment has been carried out:

Disodium sebacate

## **SECTION 16: Other information**

## Changes

Rev. 1,0; Initial release 07.05.2018

Rev. 2,0; Revision 03.04.2020, Changes in chapter: 2-16 Rev. 3,0; Revision 02.03.2023, Changes in chapter: 1-16

## Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement

concerning the International Carriage of Dangerous Goods by Road)

CAS: Chemical Abstracts Service

CLP: Classification, Labeling, Packaging

**DNEL: Derived No Effect Level** 

d: day(s)

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

ECHA: European Chemicals Agency

ECOSAR: Ecological Structure Activity Relationships

EWC: European Waste Catalogue

IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

IUCLID: International Uniform ChemicaL Information Database



according to UK REACH Regulation

Page 11 of 11

Revision date: 02.03.2023

Print date: 13.03.2023

VGI 260

GHS: Globally Harmonized System of Classification and Labelling of Chemicals GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany)

OECD: Organisation for Economic Co-operation and Development

PNEC: Predicted No Effect Concentration PBT: Persistent, bio-cumulative, toxic

QSAR: Quantitative Structure-Activity Relationship

RID: Regulation Concerning the International Transport of Dangerous Goods by Rail

RTECS: Registry of Toxic Effects of Chemical Substances

SVHC: Substance of Very High Concern TRGS: Technische Regeln für Gefahrstoffe

**UN: United Nations** 

vPvB: very persistent and very bio-cumulative

VOC: Volatile Organic Compounds

w: week(s)

None listed.

#### Relevant H and EUH statements (number and full text)

H319 Causes serious eye irritation.

EUH210 Safety data sheet available on request.

**Further Information** 

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)