

according to UK REACH Regulation

Print date: 13.03.2023

# VGS 180

SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

VGS 180

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### Use of the substance/mixture

Lubricant, lubrifiants and release products

#### Uses advised against

Any non-intended use.

# 1.3. Details of the supplier of the safety data sheet

Company name:	Meusburger Georg GmbH &	Meusburger Georg GmbH & Co KG		
Street:	Kesselstrasse 42			
Place:	A-6960 Wolfurt			
Telephone: e-mail: Internet:	+43 5574 6706-0 office@meusburger.com www.meusburger.com	Telefax: +43 5574 6706-12		
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Otto-Hahn-Str. 36	e-mail: info@tge-consult.de Tel.: +49 2534 41594-0 www.tge-consult.de		
.4. Emergency telephone	D-48161 Muenster Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240			

# 1.4. Emergency telephone

number:

#### **Further Information**

Safety Data Sheet according to UK-REACH Regulation

# **SECTION 2: Hazards identification**

#### 2.1. Classification of the substance or mixture

#### **GB CLP Regulation**

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

# 2.2. Label elements

#### **GB CLP Regulation**

EUH210

#### Special labelling of certain mixtures

Safety data sheet available on request.

#### Additional advice on labelling

Labelling according to GHS (GB CLP) regulation .: none

# 2.3. Other hazards

The mixture contains the following substances fulfilling the PBT criteria according to UK REACH: zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate).

The substance is suspected to fulfil the PBT criteria. The substance is listed in the PBT assessment list, but the assessment is still ongoing (ECHA).

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

Special danger of slipping by leaking/spilling product.

#### **SECTION 3: Composition/information on ingredients**

Page 1 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

# 3.2. Mixtures

#### Hazardous components

nuzuruous component	5	
CAS No	Chemical name	Quantity
EC No	GHS Classification	
REACH No		
Index No		
4259-15-8	zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate)	1 - < 2,5 %
224-235-5	Eye Dam. 1, Aquatic Chronic 2; H318 H411	

# Full text of H and EUH statements: see section 16.

# Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
	Specific Conc. Limits, M-factors and ATE		
4259-15-8	224-235-5	zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate)	
dermal: LD50 = (> 5000) mg/kg; oral: LD50 = (> 3100) mg/kg Eye Dam. 1; H318: >= 50 - 100			

#### **Further Information**

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

# SECTION 4: First aid measures

#### 4.1. Description of first aid measures

#### **General information**

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

#### After inhalation

In case of accident by inhalation: remove casualty to fresh air and keep at rest. In case of respiratory tract irritation, consult a physician.

#### After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

#### After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an ophthalmologist.

#### After ingestion

Rinse mouth thoroughly with water. Let water be drunken in little sips (dilution effect). Do NOT induce vomiting. In all cases of doubt, or when symptoms persist, seek medical advice.

# 4.2. Most important symptoms and effects, both acute and delayed

No information available.

# 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

# SECTION 5: Firefighting measures



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

#### 5.1. Extinguishing media

#### Suitable extinguishing media

Carbon dioxide (CO2). BC-powder. Atomized water.

Unsuitable extinguishing media High power water jet.

#### 5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide Carbon dioxide (CO2). Nitrogen oxides (NOx).

#### 5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

#### Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Co-ordinate fire-fighting measures to the fire surroundings.

# SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

#### General advice

Avoid dust formation.

Do not breathe dust.

High slip hazard because of leaking or spilled product.

#### For non-emergency personnel

Wear personal protection equipment (refer to section 8).

# For emergency responders

No special measures are necessary.

#### 6.2. Environmental precautions

Discharge into the environment must be avoided.

## 6.3. Methods and material for containment and cleaning up

#### For containment

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents). Treat the recovered material as prescribed in the section on waste disposal.

#### For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

# 6.4. Reference to other sections

Safe handling: see section 7 Personal protection equipment: see section 8 Disposal: see section 13

# SECTION 7: Handling and storage

# 7.1. Precautions for safe handling

# Advice on safe handling

Wear suitable protective clothing. (See section 8.)

# Advice on protection against fire and explosion

Usual measures for fire prevention.

# Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

Page 3 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

# Further information on handling

General protection and hygiene measures: See section 8.

#### 7.2. Conditions for safe storage, including any incompatibilities

## Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

#### Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

#### Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorbtion of humidity. Recommended storage temperature: 20 °C Protect against: frost. UV-radiation/sunlight. heat. Humidity

# 7.3. Specific end use(s)

See section 1.

# SECTION 8: Exposure controls/personal protection

# 8.1. Control parameters

#### Additional advice on limit values

To date, no national critical limit values exist.

## 8.2. Exposure controls



#### Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

Provide adequate ventilation.

# Individual protection measures, such as personal protective equipment

# Eye/face protection

Wear safety glasses; chemical goggles (if splashing is possible). BS/EN 166

#### Hand protection

In case of prolonged or frequently repeated skin contact:

Wear suitable gloves.

Suitable material:

NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm

Breakthrough time >= 8 h

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Before using check leak tightness / impermeability. In the case of wanting to use the gloves again, clean them before taking off and air them well.

#### Skin protection

Suitable protective clothing: Lab apron.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS

Page 4 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

# 500 (D).

# **Respiratory protection**

With correct and proper use, and under normal conditions, breathing protection is not required.

#### Thermal hazards

No special precautionary measures are necessary.

#### Environmental exposure controls

No special precautionary measures are necessary.

# **SECTION 9: Physical and chemical properties**

## 9.1. Information on basic physical and chemical properties

9.1. Information on basic physical and cher	
Physical state: Colour:	liquid (Paste) cream
Odour:	characteristic
Odour threshold:	not determined
Melting point/freezing point:	not determined
Boiling point or initial boiling point and	not determined
boiling range:	not dotominou
Flammability:	not determined
Lower explosion limits:	not determined
Upper explosion limits:	not determined
Flash point:	0° 00 <
Auto-ignition temperature:	not determined
Decomposition temperature:	not determined
pH-Value:	not determined
Viscosity / kinematic:	not determined
Water solubility:	insoluble
Solubility in other solvents	Insoluble
not determined	
Dissolution rate:	not relevant
Partition coefficient n-octanol/water:	SECTION 12: Ecological information
Dispersion stability:	not relevant
Vapour pressure:	not determined
Density (at 20 °C):	0,92 g/cm³
Bulk density:	not determined
Relative vapour density:	not determined
Particle characteristics:	not relevant
9.2. Other information	
Information with regard to physical haza	ard classes
Explosive properties	
none	
Sustaining combustion:	Not sustaining combustion
Self-ignition temperature	
Solid:	not relevant
Gas:	not relevant
Oxidizing properties	
none	
Other safety characteristics	

Page 5 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

Evaporation rate: Solvent separation test: Solvent content: Solid content: Sublimation point: Softening point: Pour point: Drop point/drop range: Viscosity / dynamic: Flow time:

#### **Further Information**

No information available.

# SECTION 10: Stability and reactivity

#### 10.1. Reactivity

No information available.

#### 10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

# 10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions. Refer to chapter 10.5.

# 10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat.

## 10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong. Strong acid.

#### 10.6. Hazardous decomposition products

Does not decompose when used for intended uses.

# SECTION 11: Toxicological information

## 11.1. Information on hazard classes as defined in GB CLP Regulation

#### Toxicocinetics, metabolism and distribution

No data available.

#### Acute toxicity

Based on available data, the classification criteria are not met.

CAS No	Chemical name				
	Exposure route         Dose         Species         Source         Method			Method	
4259-15-8	zinc bis[0,0-bis(2-ethylhexyl)] bis(dithiophosphate)				
	oral LD50 (> 3100) mg/kg		Rat.	ECHA dossier	
	dermal	LD50 (> 5000) mg/kg	Rabbit.	ECHA dossier	

#### Irritation and corrosivity

Page 6 of 11

Revision date: 03.03.2023

not determined not determined not determined not determined not determined not determined >= 240 °C not determined not determined



according to UK REACH Regulation

Print date: 13.03.2023

#### VGS 180

Based on available data, the classification criteria are not met.

zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate): This substance is not a skin irritant. It is an eye irritant at 100%, but not an eye irritant at a 50% concentration. (ECHA dossier)

#### Sensitising effects

Based on available data, the classification criteria are not met.

#### Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate):

In vitro mutagenicity/genotoxicity: Method: OECD Guideline 471 (Bacterial Reverse Mutation Assay); Result: negative.

Literature information: ECHA dossier

Developmental toxicity/teratogenicity/Reproductive toxicity:; Species: Rat (Sprague-Dawley); Method: OECD Guideline 421 (Reproduction / Developmental Toxicity Screening Test); Result: NOAEL = 30 mg/kg Literature information: ECHA dossier

#### STOT-single exposure

Based on available data, the classification criteria are not met.

#### STOT-repeated exposure

Based on available data, the classification criteria are not met.

zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate): Subacute oral toxicity: Method: OECD Guideline 407 (Repeated Dose 28-Day Oral Toxicity in Rodents); Species: Rat; Results: NOAEL = 125 mg/kg Literature information: ECHA dossier

#### Aspiration hazard

Based on available data, the classification criteria are not met.

#### Specific effects in experiment on an animal

No data available.

#### 11.2. Information on other hazards

#### **Endocrine disrupting properties**

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

#### Other information

No data available.

# **SECTION 12: Ecological information**

# 12.1. Toxicity

The product has not been tested.

CAS No	Chemical name				
	Aquatic toxicity         Dose         [h]   [d]         Species         Source         Method				
4259-15-8	zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate)				
	Acute fish toxicity LC50 46 mg/l 96 h Cyprinodon variegatus ECHA dossier				
12.2. Persistence and degradability					

#### 12.2. Persistence and degradability

The product has not been tested.

Page 7 of 11



according to UK REACH Regulation

Page 8 of 11

Revision date: 03.03.2023

Print date: 13.03.2023

#### VGS 180

	Method	Value	d	Source
Evaluation				
4259-15-	zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate)			
	OECD 301D / EEC 92/69 annex V, C.4-E	< 5%	27	ECHA dossier
	Not easily bio-degradable (according to OECD-criteria).			

# 12.3. Bioaccumulative potential

#### Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
4259-15-8	zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate)	3,59

# 12.4. Mobility in soil

No data available.

#### 12.5. Results of PBT and vPvB assessment

The mixture contains the following substances fulfilling the PBT criteria according to UK REACH: zinc bis[0,0-bis(2-ethylhexyl)] bis(dithiophosphate).

The substance is suspected to fulfil the PBT criteria. The substance is listed in the PBT assessment list, but the assessment is still ongoing (ECHA).

#### 12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

#### 12.7. Other adverse effects

No data available.

# **Further information**

Do not allow to enter into surface water or drains.

# SECTION 13: Disposal considerations

# 13.1. Waste treatment methods

#### **Disposal recommendations**

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal. Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process. Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

## List of Wastes Code - residues/unused products

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

#### List of Wastes Code - used product

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

# List of Wastes Code - contaminated packaging

150106 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); mixed packaging

# meusburger

# Safety Data Sheet

according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

# Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

#### **SECTION 14: Transport information**

## Land transport (ADR/RID)

 14.1. UN number or ID number:

 14.2. UN proper shipping name:

 14.3. Transport hazard class(es):

 14.4. Packing group:

 Inland waterways transport (ADN)

 14.1. UN number or ID number:

 14.2. UN proper shipping name:

 14.3. Transport hazard class(es):

 14.4. Packing group:

 Marine transport (IMDG)

 14.1. UN number or ID number:

 14.2. UN proper shipping name:

<u>14.3. Transport hazard class(es):</u> Air transport (ICAO-TI/IATA-DGR)

14.1. UN number or ID number: 14.2. UN proper shipping name: 14.3. Transport hazard class(es):

# 14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS:

# 14.6. Special precautions for user

Refer to section 6 - 8

# 14.7. Maritime transport in bulk according to IMO instruments not relevant

# SECTION 15: Regulatory information

# 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

No

EU regulatory information	
2010/75/EU (VOC):	not determined
2004/42/EC (VOC):	not determined
Information according to 2012/18/EU (SEVESO III):	Not subject to 2012/18/EU (SEVESO III)
Additional information	
Safety Data Sheet according to UK-RE	ACH Regulation
This mixture is classified as not hazardo	ous according to GHS (GB CLP).
UK REACH Appendix XVII, No (mixture	): 3, 75
National regulatory information	

Water hazard class (D):	<ol> <li>slightly hazardous to water</li> </ol>
-------------------------	---

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations. No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

No dangerous good in sense of these transport regulations.

Page 9 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

#### 15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

#### **SECTION 16: Other information**

#### Changes

Rev. 1,0; Initial release 08.05.2018 Rev. 2,0; Revision 03.04.2020 Changes in chapter: 2-16 Rev. 3,0; Revision 28.01.2022 Changes in chapter: 2-16 Rev. 4,0; Revision 03.03.2023 Changes in chapter: 1-16 Abbreviations and acronyms ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road) AGW: Arbeitsplatzgrenzwert CAS: Chemical Abstracts Service CLP: Classification, Labelling and Packaging of substances and mixtures DNEL: Derived No Effect Level d: dav(s) EINECS: European INventory of Existing Commercial chemical Substances ELINCS: European List of Notified Chemical Substances ECHA: European Chemicals Agency EWC: European Waste Catalogue IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER IMDG: International Maritime Code for Dangerous Goods IATA: International Air Transport Association IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA) ICAO: International Civil Aviation Organization ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO) GHS: Globally Harmonized System of Classification and Labelling of Chemicals GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany) h: hour LOAEL: Lowest observed adverse effect level LOAEC: Lowest observed adverse effect concentration LC50: Lethal concentration, 50 percent LD50: Lethal dose, 50 percent NOAEL: No observed adverse effect level NOAEC: No observed adverse effect concentration NLP: No-Longer Polymers N/A: not applicable OECD: Organisation for Economic Co-operation and Development PNEC: predicted no effect concentration PBT: Persistent bioaccumulative toxic RID: Reglement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail) REACH: Registration, Evaluation, Authorisation of Chemicals SVHC: substance of very high concern TRGS: Technische Regeln für Gefahrstoffe UN: United Nations VOC: Volatile Organic Compounds

Page 10 of 11



according to UK REACH Regulation

Print date: 13.03.2023

VGS 180

Page 11 of 11

Revision date: 03.03.2023

# Relevant H and EUH statements (number and full text)

H318	
H411	
EUH210	

Causes serious eye damage. Toxic to aquatic life with long lasting effects. Safety data sheet available on request.

**Further Information** 

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)