

according to UK REACH Regulation

Print date: 13.03.2023

## VLP 32

SECTION 1: Identification of the substance/mixture and of the company/undertaking

## 1.1. Product identifier

VLP 32

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

## Use of the substance/mixture

Hydraulic fluids

## Uses advised against

Any non-intended use.

## 1.3. Details of the supplier of the safety data sheet

Company name:	Meusburger Georg GmbH & Co KG	
Street:	Kesselstrasse 42	
Place:	A-6960 Wolfurt	
Telephone: e-mail: Internet:	+43 5574 6706-0 office@meusburger.com www.meusburger.com	Telefax: +43 5574 6706-12
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Otto-Hahn-Str. 36 D-48161 Muenster	e-mail: info@tge-consult.de Tel.: +49 2534 41594-0 www.tge-consult.de
1.4. Emergency telephone	Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240	

# number:

# Further Information

Safety Data Sheet according to UK-REACH Regulation

## SECTION 2: Hazards identification

## 2.1. Classification of the substance or mixture

#### **GB CLP Regulation**

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

#### 2.2. Label elements

#### Additional advice on labelling

Labelling according to GHS (GB CLP) regulation .: none

#### 2.3. Other hazards

Prolonged/repetitive skin contact may cause skin defattening or dermatitis. May cause respiratory irritation. May cause long-term adverse effects in the aquatic environment. For information or further instructions, see also section 11 or 12.

#### SECTION 3: Composition/information on ingredients

## 3.2. Mixtures

## Chemical characterization

The product does not contain dangerous substances according to UK REACH, Annex II, Part A , 3.1/3.2. that must be mentioned in Chapter 3.

none (according to UK REACH Regulation)

Page 1 of 9



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

## **Further Information**

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

## SECTION 4: First aid measures

#### 4.1. Description of first aid measures

#### **General information**

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

## After inhalation

In case of accident by inhalation: remove casualty to fresh air and keep at rest. In case of respiratory tract irritation, consult a physician.

#### After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

#### After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an ophthalmologist.

#### After ingestion

Rinse mouth thoroughly with water. Let water be drunken in little sips (dilution effect). Do NOT induce vomiting. In all cases of doubt, or when symptoms persist, seek medical advice.

#### 4.2. Most important symptoms and effects, both acute and delayed

No information available.

## 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## **SECTION 5: Firefighting measures**

#### 5.1. Extinguishing media

## Suitable extinguishing media

Carbon dioxide (CO2). Dry extinguishing powder. Alcohol resistant foam. Atomized water.

#### Unsuitable extinguishing media

High power water jet.

## 5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide. Carbon dioxide (CO2).

## 5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

## Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Co-ordinate fire-fighting measures to the fire surroundings.

## SECTION 6: Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

## General advice

Safe handling: see section 7

## For non-emergency personnel

Wear personal protection equipment (refer to section 8).

Page 2 of 9



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

## For emergency responders

No special measures are necessary.

## 6.2. Environmental precautions

Discharge into the environment must be avoided.

## 6.3. Methods and material for containment and cleaning up

#### For containment

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents). Treat the recovered material as prescribed in the section on waste disposal.

#### For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

#### 6.4. Reference to other sections

Safe handling: see section 7 Personal protection equipment: see section 8 Disposal: see section 13

## SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

#### Advice on safe handling

Wear suitable protective clothing. (See section 8.)

## Advice on protection against fire and explosion

Usual measures for fire prevention.

## Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

## Further information on handling

General protection and hygiene measures: See section 8.

## 7.2. Conditions for safe storage, including any incompatibilities

#### Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

## Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

#### Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorbtion of humidity. Recommended storage temperature: 20 °C Protect against: frost. UV-radiation/sunlight. heat. Humidity

#### 7.3. Specific end use(s)

See section 1.

## SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

## Additional advice on limit values

To date, no national critical limit values exist.

Page 3 of 9



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

## 8.2. Exposure controls

#### Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

## Provide adequate ventilation.

## Individual protection measures, such as personal protective equipment

#### Eye/face protection

Wear safety glasses; chemical goggles (if splashing is possible). BS/EN 166

## Hand protection

In case of prolonged or frequently repeated skin contact:

Wear suitable gloves.

Suitable material:

FKM (fluororubber). - Thickness of glove material: 0,4 mm

Breakthrough time >= 8 h

Butyl rubber. - Thickness of glove material: 0,5 mm

Breakthrough time >= 8 h

CR (polychloroprenes, Chloroprene rubber). - Thickness of glove material: 0,5 mm

Breakthrough time >= 8 h

NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm

Breakthrough time >= 8 h

PVC (Polyvinyl chloride). - Thickness of glove material: 0,5 mm

Breakthrough time >= 8 h

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Before using check leak tightness / impermeability. In the case of wanting to use the gloves again, clean them before taking off and air them well.

#### Skin protection

Suitable protective clothing: Lab apron.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500 (D).

#### **Respiratory protection**

With correct and proper use, and under normal conditions, breathing protection is not required.

## Thermal hazards

No special precautionary measures are necessary.

## Environmental exposure controls

No special precautionary measures are necessary.

## SECTION 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

Physical state:	liquid
Colour:	yellow brown
Odour:	characteristic
Odour threshold:	not determined

Melting point/freezing point:
Boiling point or initial boiling point and
boiling range:

not determined > 320 °C Page 4 of 9



Page 5 of 9

Revision date: 07.03.2023

## Safety Data Sheet

according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

Flammability: not determined Lower explosion limits: not determined Upper explosion limits: not determined Flash point: >180 °C DIN 51755 > 250 °C Auto-ignition temperature: Decomposition temperature: not determined pH-Value: not determined Viscosity / kinematic: 29.8 - 352 mm<sup>2</sup>/s (at 40 °C) Water solubility: not miscible Solubility in other solvents not determined Dissolution rate: not relevant Partition coefficient n-octanol/water: SECTION 12: Ecological information Dispersion stability: not relevant Vapour pressure: not determined Density (at 15 °C): 0.86 - 0.88 g/cm<sup>3</sup> Bulk density: not determined Relative vapour density: not determined Particle characteristics: not relevant 9.2. Other information Information with regard to physical hazard classes Explosive properties none Sustaining combustion: Not sustaining combustion Self-ignition temperature Solid: not relevant Gas: not relevant Oxidizing properties none Other safety characteristics not determined Evaporation rate: Solvent separation test: not determined Solvent content: not determined Solid content: not determined Sublimation point: not determined Softening point: not determined Pour point: not determined Viscosity / dynamic: not determined Flow time: not determined **Further Information** No information available.

# SECTION 10: Stability and reactivity

## 10.1. Reactivity

No information available.

#### 10.2. Chemical stability



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

The product is chemically stable under recommended conditions of storage, use and temperature.

## 10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.

Refer to chapter 10.5.

#### 10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat.

## 10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong.

## 10.6. Hazardous decomposition products

Does not decompose when used for intended uses.

## **SECTION 11: Toxicological information**

## 11.1. Information on hazard classes as defined in GB CLP Regulation

## Toxicocinetics, metabolism and distribution

No data available.

#### Acute toxicity

Based on available data, the classification criteria are not met.

#### Irritation and corrosivity

Based on available data, the classification criteria are not met.

#### Sensitising effects

Based on available data, the classification criteria are not met.

## Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

## STOT-single exposure

Based on available data, the classification criteria are not met.

#### STOT-repeated exposure

Based on available data, the classification criteria are not met.

#### Aspiration hazard

Based on available data, the classification criteria are not met.

#### Specific effects in experiment on an animal

No data available.

## 11.2. Information on other hazards

#### Endocrine disrupting properties

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

## Other information

No data available.

## **SECTION 12: Ecological information**

## 12.1. Toxicity

The product has not been tested.

## 12.2. Persistence and degradability

The product has not been tested.

Page 6 of 9



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

Page 7 of 9

Revision date: 07.03.2023

## 12.3. Bioaccumulative potential

No indication of bioaccumulation potential.

12.4. Mobility in soil

No data available.

## 12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

## 12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1

%.

## 12.7. Other adverse effects

No data available.

## **Further information**

Do not allow to enter into surface water or drains.

## **SECTION 13: Disposal considerations**

## 13.1. Waste treatment methods

#### **Disposal recommendations**

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal. Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process. Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

#### List of Wastes Code - residues/unused products

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

#### List of Wastes Code - used product

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

## List of Wastes Code - contaminated packaging

150106 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); mixed packaging

## Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

## **SECTION 14: Transport information**

## Land transport (ADR/RID)

14.1. UN number or ID number:	No dangerous good in sense of these transport regulations.
14.2. UN proper shipping name:	No dangerous good in sense of these transport regulations.
14.3. Transport hazard class(es):	No dangerous good in sense of these transport regulations.
14.4. Packing group:	No dangerous good in sense of these transport regulations.

according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

Inland waterways transport (ADN)		
14.1. UN number or ID number:	No dangerous good in sense of these transport regulations.	
14.2. UN proper shipping name:	No dangerous good in sense of these transport regulations.	
14.3. Transport hazard class(es):	No dangerous good in sense of these transport regulations.	
14.4. Packing group:	No dangerous good in sense of these transport regulations.	
Marine transport (IMDG)		
14.1. UN number or ID number:	No dangerous good in sense of these transport regulations.	
14.2. UN proper shipping name:	No dangerous good in sense of these transport regulations.	
14.3. Transport hazard class(es):	No dangerous good in sense of these transport regulations.	
Air transport (ICAO-TI/IATA-DGR)		
14.1. UN number or ID number:	No dangerous good in sense of these transport regulations.	
14.2. UN proper shipping name:	No dangerous good in sense of these transport regulations.	
14.3. Transport hazard class(es):	No dangerous good in sense of these transport regulations.	
14.5. Environmental hazards		
ENVIRONMENTALLY HAZARDOUS:	No	
14.6. Special precautions for user		
Refer to section 6 - 8		
14.7. Maritime transport in bulk according to IMO instruments		
not relevant		

## SECTION 15: Regulatory information

## 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

## EU regulatory information

2010/75/EU (VOC):	not determined
2004/42/EC (VOC):	not determined
Information according to 2012/18/EU	Not subject to 2012/18/EU (SEVESO III)
(SEVESO III):	

Additional information

Safety Data Sheet according to UK-REACH Regulation This mixture is classified as not hazardous according to GHS (GB CLP). UK REACH Appendix XVII, No (mixture): not relevant

## National regulatory information

Water hazard class (D):

1 - slightly hazardous to water

#### 15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

## **SECTION 16: Other information**

## Changes

Rev. 1,0; Initial release: 11.05.2018 Rev. 2.0; Revision 06.04.2020 Changes in chapter: 2-16 Rev. 3.0; Revision 07.03.2023 Changes in chapter: 2-16

## Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

# IS.

Page 8 of 9

Revision date: 07.03.2023

meusburger



according to UK REACH Regulation

Print date: 13.03.2023

VLP 32

CAS: Chemical Abstracts Service CLP: Classification, Labeling, Packaging DNEL: Derived No Effect Level d: day(s) EINECS: European Inventory of Existing Commercial Chemical Substances ELINCS: European List of Notified Chemical Substances ECHA: European Chemicals Agency ECOSAR: Ecological Structure Activity Relationships EWC: European Waste Catalogue IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER IMDG: International Maritime Code for Dangerous Goods IATA: International Air Transport Association IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA) ICAO: International Civil Aviation Organization ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO) GHS: Globally Harmonized System of Classification and Labelling of Chemicals GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany) OECD: Organisation for Economic Co-operation and Development PNEC: Predicted No Effect Concentration PBT: Persistent, bio-cumulative, toxic QSAR: Quantitative Structure-Activity Relationship RID: Regulation Concerning the International Transport of Dangerous Goods by Rail SVHC: Substance of Very High Concern TRGS: Technische Regeln für Gefahrstoffe UN: United Nations vPvB: very persistent and very bio-cumulative VOC: Volatile Organic Compounds w: week(s)

## **Further Information**

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)

Page 9 of 9