

### PRODUCT DESCRIPTION

- » Battery-operated thus portable for on-site measurement
- » Surface roughness measuring with skid system
- » Detachable feed unit
- » Large colour display, simple menu navigation (16 languages)

### INCLUDED IN THE DELIVERY

- » Mains adapter, calibration standard, and carrying case



Mitutoyo



Probe tip	Fn	Scanning speed	Cut-off length	Roughness standards	lk <sup>1)</sup>	MB <sup>2)</sup>	MB max. <sup>3)</sup>	No.	EUR
Diamond	0.75 mN	0.25; 0.5; 0.75 mm/s	λc: 0.08; 0.25; 0.8; 2.5 mm	DIN EN ISO, VDA, ANSI, JIS	1 m	16	17,5	MRM 2100/17,5	< >

1) lk: cable length

2) MB: measuring range

3) MB max.: Maximum measuring range