meusburger

HSS-E FLUTELESS TAP FOR BSP THREADS, FOR BLIND AND THROUGH HOLES

WZG 32520



PRODUCT DESCRIPTION

» Fluteless tap with oil grooves for BSP threads

ΝЛ		-	א וכ	
IVI	AI	EF	KI A	\L
		_		

» HSS-E (5% Co), TiN coated

	_ (= / = /	//						
SW	d3	d5	I	11	GZ ¹⁾	d	No.	EUR
5.5	7	9.3	90	18	28	G 1/8″	WZG 32520/1/8	< >
9	11	12.5	100	20	19	G 1/4″	WZG 32520/1/4	< >
9	12	16	100	22	19	G 3/8″	WZG 32520/3/8	< >

1) GZ: Threads per inch



REFERENCE VALUES FOR WORKING WITH FLUTELESS TAPS

WZG 3	32120 21204 32520	Material	Strength	Vc¹ m/min.
		1.1730	640 N/mm ²	20
		1.2083	780 N/mm ²	20
		1.2162	660 N/mm ²	20
		1.2311	1080 N/mm ²	10
		1.2312	1080 N/mm ²	10
		1.2343	780 N/mm ²	20
		1.2379	780 N/mm ²	20
		1.2767	830 N/mm ²	10
		1.2842	775 N/mm ²	20
		1.2767	830 N/mm ²	8
		1.2842	775 N/mm ²	10

Μ

S

I) Vc: cutting speed (m/mi

You can find further materials and cutting values in the cutting data calculator.



WHICH CUTTING FLUID IS RIGHT FOR WORKING WITH FLUTELESS TAPS?

When working with fluteless taps the main task of the cutting fluids is the lubrication. The more lubricant used with the maximum possible grease concentration, the longer the service life of the fluteless taps.

For water-miscible cutting fluids the grease concentration must not be less than 6%. A grease content of >12% is ideal to reach the optimal service life.