


HSS FLAT COUNTERSINK 2°

WZB 318122



PRODUCT DESCRIPTION

» Matching the E 1670 and E 16709 Ventilation valve

MATERIAL

» HSS


P M K N S H

Z	d2	d3	I	I1	d	No.	EUR
3	6	10	69	5	8	WZB 318122/ 8	< >
3	8	12	100	5	12	WZB 318122/12	< >
3	10	12	122	6	16	WZB 318122/16	< >



REFERENCE VALUES FOR COUNTERSINKING

WZB 31722
WZB 317226
WZB 318120
WZB 318121
WZB 318122



Material	Strength	Vc ¹ m/min.	≤ d							
			8	10	15	20	24	26	33	40
f ² (mm/u)										
1.1730	640 N/mm ²	20	0.125	0.150	0.160	0.180	0.200	0.225	0.250	0.250
1.2083	780 N/mm ²	11	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200
1.2085	1080 N/mm ²	9	0.095	0.115	0.125	0.140	0.150	0.170	0.190	0.190
1.2162	660 N/mm ²	11	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200
1.2311	1080 N/mm ²	9	0.095	0.115	0.125	0.140	0.150	0.170	0.190	0.190
1.2312	1080 N/mm ²	9	0.095	0.115	0.125	0.140	0.150	0.170	0.190	0.190
1.2316	1010 N/mm ²	9	0.095	0.115	0.125	0.140	0.150	0.170	0.190	0.190
1.2343	780 N/mm ²	11	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200
1.2379	780 N/mm ²	8	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200
1.2767	830 N/mm ²	11	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200
1.2842	775 N/mm ²	11	0.100	0.120	0.130	0.150	0.160	0.180	0.200	0.200

1) Vc: cutting speed (m/min.)

2) f: feed per revolution (mm/rev.)

i You can find further materials and cutting values in the cutting data calculator.