

Safety Data Sheet

according to UK REACH Regulation

Page 1 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

V76905 & V76908

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Abrasive, Polishing agent

Uses advised against

Any non-intended use.

1.3. Details of the supplier of the safety data sheet

Company name:	Meusburger Georg GmbH & Co KG	
Street:	Kesselstrasse 42	
Place:	A-6960 Wolfurt	
Telephone:	+43 5574 6706-0	Telefax: +43 5574 6706-12
e-mail:	office@meusburger.com	
Internet:	www.meusburger.com	
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Otto-Hahn-Str. 36 D-48161 Muenster	e-mail: info@tge-consult.de Tel.: +49 2534 41594-0 www.tge-consult.de

1.4. Emergency telephone number:

Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240

Further Information

Safety Data Sheet according to UK-REACH Regulation

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GB CLP Regulation

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

2.2. Label elements

Additional advice on labelling

Labelling according to GHS (GB CLP) regulation.: none

2.3. Other hazards

The substances in the mixture (> 0.1%) do not meet the PBT/vPvB criteria according to UK REACH.

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

No risks worthy of mention. Please observe the information on the safety data sheet at all times.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Chemical characterization

The product does not contain dangerous substances according to UK REACH, Annex II, Part A, 3.1/3.2. that must be mentioned in Chapter 3.

none (according to UK REACH Regulation)

Safety Data Sheet

according to UK REACH Regulation

Page 2 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

Further Information

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After inhalation

In case of accident by inhalation: remove casualty to fresh air and keep at rest. In case of respiratory tract irritation, consult a physician.

After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an ophthalmologist.

After ingestion

Rinse mouth thoroughly with water. Let water be drunk in little sips (dilution effect). Do NOT induce vomiting. In all cases of doubt, or when symptoms persist, seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Nausea. Dizziness. vomiting.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂). Dry extinguishing powder. Alcohol resistant foam. Atomized water.

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide. Carbon dioxide (CO₂). Gas/vapours, toxic.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Co-ordinate fire-fighting measures to the fire surroundings.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Safe handling: see section 7

Safety Data Sheet

according to UK REACH Regulation

Page 3 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

For non-emergency personnel

Wear personal protection equipment (refer to section 8).

For emergency responders

No special measures are necessary.

6.2. Environmental precautions

Discharge into the environment must be avoided.

6.3. Methods and material for containment and cleaning up

For containment

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents).
Treat the recovered material as prescribed in the section on waste disposal.

For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

Other information

Spillages make surfaces slippery.
Treat the recovered material as prescribed in the section on waste disposal.
Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Safe handling: see section 7
Personal protection equipment: see section 8
Disposal: see section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Wear suitable protective clothing. (See section 8.)

Advice on protection against fire and explosion

Usual measures for fire prevention.
In use, may form flammable/explosive vapour-air mixture. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

Further information on handling

General protection and hygiene measures: See section 8.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorption of humidity.
Recommended storage temperature: 20 °C
Protect against: frost. UV-radiation/sunlight. heat. Humidity

7.3. Specific end use(s)

Safety Data Sheet

according to UK REACH Regulation

Page 4 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

See section 1.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Additional advice on limit values

To date, no national critical limit values exist.

8.2. Exposure controls



Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

Provide adequate ventilation.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear safety glasses; chemical goggles (if splashing is possible). BS/EN 166

Hand protection

In case of prolonged or frequently repeated skin contact:

Wear suitable gloves.

Suitable material:

FKM (fluororubber). - Thickness of glove material: 0,4 mm

Breakthrough time \geq 8 h

Butyl rubber. - Thickness of glove material: 0,5 mm

Breakthrough time \geq 8 h

CR (polychloroprenes, Chloroprene rubber). - Thickness of glove material: 0,5 mm

Breakthrough time \geq 8 h

NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm

Breakthrough time \geq 8 h

PVC (Polyvinyl chloride). - Thickness of glove material: 0,5 mm

Breakthrough time \geq 8 h

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Before using check leak tightness / impermeability. In the case of wanting to use the gloves again, clean them before taking off and air them well.

Skin protection

Suitable protective clothing: Lab apron.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500 (D).

Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required.

Respiratory protection necessary at:

-Exceeding exposure limit values

-Insufficient ventilation and aerosol or mist formation

Suitable respiratory protective equipment: Combination filtering device (EN 14387) Type A-P2

Safety Data Sheet

according to UK REACH Regulation

Page 5 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

Thermal hazards

No special precautionary measures are necessary.

Environmental exposure controls

No special precautionary measures are necessary.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Paste
Colour:	white, grey
Odour:	characteristic
Odour threshold:	not determined
Melting point/freezing point:	> 30 - < 60 °C
Boiling point or initial boiling point and boiling range:	not determined
Flammability:	not determined
Lower explosion limits:	not determined
Upper explosion limits:	not determined
Flash point:	>200 °C
Auto-ignition temperature:	>= 320 °C
Decomposition temperature:	~ 360 °C
pH-Value (at 20 °C):	4 - 7 (100 g/l)
Viscosity / kinematic:	not determined
Water solubility:	miscible.
Solubility in other solvents	not determined
Dissolution rate:	not relevant
Partition coefficient n-octanol/water:	SECTION 12: Ecological information
Dispersion stability:	not relevant
Vapour pressure: (at 20 °C)	<0,1 hPa
Density:	~ 1,2 g/cm ³
Bulk density:	not determined
Relative vapour density:	not determined
Particle characteristics:	not relevant

9.2. Other information

Information with regard to physical hazard classes

Explosive properties	none
Sustaining combustion:	No data available
Self-ignition temperature	
Solid:	not relevant
Gas:	>=320 °C
Oxidizing properties	none

Safety Data Sheet

according to UK REACH Regulation

Page 6 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

Other safety characteristics

Evaporation rate:	not determined
Solvent separation test:	not determined
Solvent content:	not determined
Solid content:	not determined
Sublimation point:	not determined
Softening point:	not determined
Pour point:	not determined
Viscosity / dynamic:	not determined
Flow time:	not determined

Further Information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

Refer to chapter 10.5.

In use, may form flammable/explosive vapour-air mixture.

10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat. Keep away from sources of heat (e.g. hot surfaces), sparks and open flames.

10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong.

10.6. Hazardous decomposition products

Can be released in case of fire: Carbon monoxide. Carbon dioxide (CO₂). Gas/vapours, toxic.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in GB CLP Regulation

Toxicokinetics, metabolism and distribution

No data available.

Acute toxicity

Based on available data, the classification criteria are not met.

Irritation and corrosivity

Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

Safety Data Sheet

according to UK REACH Regulation

Page 7 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

Specific effects in experiment on an animal

No data available.

11.2. Information on other hazards

Endocrine disrupting properties

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

Other information

No data available.

SECTION 12: Ecological information

12.1. Toxicity

The product has not been tested.

12.2. Persistence and degradability

Product is partially biodegradable.

12.3. Bioaccumulative potential

No indication of bioaccumulation potential.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.7. Other adverse effects

No data available.

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal.

Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process.

Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

Safety Data Sheet

according to UK REACH Regulation

Page 8 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

List of Wastes Code - residues/unused products

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

List of Wastes Code - used product

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

List of Wastes Code - contaminated packaging

150106 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); mixed packaging

Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of these transport regulations.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of these transport regulations.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of these transport regulations.
<u>14.4. Packing group:</u>	No dangerous good in sense of these transport regulations.

Inland waterways transport (ADN)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of these transport regulations.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of these transport regulations.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of these transport regulations.
<u>14.4. Packing group:</u>	No dangerous good in sense of these transport regulations.

Marine transport (IMDG)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of these transport regulations.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of these transport regulations.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of these transport regulations.

Air transport (ICAO-TI/IATA-DGR)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of these transport regulations.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of these transport regulations.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of these transport regulations.

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

Refer to section 6 - 8

14.7. Maritime transport in bulk according to IMO instruments

not relevant

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

2010/75/EU (VOC):	not determined
2004/42/EC (VOC):	not determined

Safety Data Sheet

according to UK REACH Regulation

Page 10 of 10

Print date: 13.03.2023

Revision date: 09.02.2023

V76905 & V76908

RID: Reglement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

REACH: Registration, Evaluation, Authorisation of Chemicals

SVHC: substance of very high concern

TRGS: Technische Regeln für Gefahrstoffe

UN: United Nations

VOC: Volatile Organic Compounds

Further Information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)