

Safety Data Sheet

according to UK REACH Regulation

Page 1 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

VGI 300

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Lubricants, greases, release products

Uses advised against

Any non-intended use.

1.3. Details of the supplier of the safety data sheet

Company name:	Meusburger Georg GmbH & Co KG	
Street:	Kesselstrasse 42	
Place:	A-6960 Wolfurt	
Telephone:	+43 5574 6706-0	Telefax: +43 5574 6706-12
e-mail:	office@meusburger.com	
Internet:	www.meusburger.com	
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Otto-Hahn-Str. 36 D-48161 Muenster	e-mail: info@tge-consult.de Tel.: +49 2534 41594-0 www.tge-consult.de

1.4. Emergency telephone number:

Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240

Further Information

Safety Data Sheet according to UK-REACH Regulation

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GB CLP Regulation

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

2.2. Label elements

Additional advice on labelling

Labelling according to GHS (GB CLP) regulation.: none

2.3. Other hazards

The substances in the mixture (> 0.1%) do not meet the PBT/vPvB criteria according to UK REACH.

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

No risks worthy of mention. Please observe the information on the safety data sheet at all times.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Chemical characterization

The product does not contain dangerous substances according to UK REACH, Annex II, Part A , 3.1/3.2. that must be mentioned in Chapter 3.

none (according to UK REACH Regulation)

Safety Data Sheet

according to UK REACH Regulation

Page 2 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

Further Information

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After inhalation

Paste: Inhalation is unlikely because of the low vapour pressure of the substance at ambient temperature. In case of respiratory tract irritation, consult a physician.

After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an ophthalmologist.

After ingestion

Rinse mouth thoroughly with water. Let water be drunk in little sips (dilution effect). Do NOT induce vomiting. In all cases of doubt, or when symptoms persist, seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

The product itself does not burn. Co-ordinate fire-fighting measures to the fire surroundings.

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide Carbon dioxide (CO₂).

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Co-ordinate fire-fighting measures to the fire surroundings.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Avoid dust formation.
Do not breathe dust.

Safety Data Sheet

according to UK REACH Regulation

Page 3 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

Special danger of slipping by leaking/spilling product.

For non-emergency personnel

Wear personal protection equipment (refer to section 8).

For emergency responders

No special measures are necessary.

6.2. Environmental precautions

Discharge into the environment must be avoided.

6.3. Methods and material for containment and cleaning up

For containment

Take up mechanically.

Treat the recovered material as prescribed in the section on waste disposal.

For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Wear personal protection equipment (refer to section 8).

Advice on protection against fire and explosion

Usual measures for fire prevention. Dust clouds may present an explosion hazard.

Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

Further information on handling

Avoid generation of dust.

General protection and hygiene measures: refer to chapter 8

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorption of humidity.

Recommended storage temperature: 20 °C

Protect against: frost. UV-radiation/sunlight. heat. Humidity

7.3. Specific end use(s)

See section 1.

SECTION 8: Exposure controls/personal protection

Safety Data Sheet

according to UK REACH Regulation

Page 4 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

8.1. Control parameters

Additional advice on limit values

To date, no national critical limit values exist.

8.2. Exposure controls

Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

Dust should be exhausted directly at the point of origin.

Individual protection measures, such as personal protective equipment

Eye/face protection

Dust protection goggles.

Hand protection

In case of prolonged or frequently repeated skin contact:

Wear suitable gloves.

Suitable material:

NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm

Breakthrough time \geq 8 h

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Before using check leak tightness / impermeability. In the case of wanting to use the gloves again, clean them before taking off and air them well.

Skin protection

Suitable protective clothing: Protective clothing.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500 (D).

Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required.

Respiratory protection necessary at:

-Exceeding exposure limit values

-Insufficient ventilation and Generation/formation of dust

Suitable respiratory protective equipment: particulates filter device (DIN EN 143). Type: P1-3

The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

Thermal hazards

Material handled at elevated temperature may cause thermal burns by contact with molten product.

Environmental exposure controls

No special precautionary measures are necessary.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Paste	
Colour:	white	
Odour:	neutral	
Odour threshold:	not determined	
Melting point/freezing point:		not determined

Safety Data Sheet

according to UK REACH Regulation

Page 5 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

Boiling point or initial boiling point and boiling range:	not determined
Flammability:	not determined
Lower explosion limits:	not relevant
Upper explosion limits:	not relevant
Flash point:	not relevant
Auto-ignition temperature:	not relevant
Decomposition temperature:	> 290 °C
pH-Value:	not determined
Viscosity / kinematic:	not relevant
Water solubility:	insoluble
Solubility in other solvents insoluble in: Hydrocarbons, Alcohol	
Dissolution rate:	not relevant
Partition coefficient n-octanol/water:	SECTION 12: Ecological information
Dispersion stability:	not relevant
Vapour pressure:	not determined
Density (at 20 °C):	1,84 g/cm ³
Bulk density:	not determined
Relative vapour density:	not relevant
Particle characteristics:	not determined

9.2. Other information

Information with regard to physical hazard classes

Explosive properties

Dust clouds may present an explosion hazard.

Sustaining combustion:

Not sustaining combustion

Self-ignition temperature

Solid:

not determined

Gas:

not relevant

Oxidizing properties

none

Other safety characteristics

Evaporation rate:

not applicable

Solvent separation test:

not applicable

Solvent content:

not determined

Solid content:

not determined

Sublimation point:

not determined

Softening point:

not determined

Pour point:

not determined

Viscosity / dynamic:

not determined

Flow time:

not applicable

Further Information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

Safety Data Sheet

according to UK REACH Regulation

Page 6 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.
Refer to chapter 10.5.

10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat.

10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong. Strong acid.

10.6. Hazardous decomposition products

Carbon monoxide. Carbon dioxide (CO₂). Gas/vapours, toxic. Pyrolysis products, toxic, contains fluorine.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in GB CLP Regulation

Toxicokinetics, metabolism and distribution

No data available.

Acute toxicity

Based on available data, the classification criteria are not met.

Irritation and corrosivity

Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

Specific effects in experiment on an animal

No data available.

11.2. Information on other hazards

Endocrine disrupting properties

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

Other information

No data available.

SECTION 12: Ecological information

12.1. Toxicity

The product has not been tested.

12.2. Persistence and degradability

Safety Data Sheet

according to UK REACH Regulation

Page 7 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

The product has not been tested.

12.3. Bioaccumulative potential

No indication of bioaccumulation potential.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.7. Other adverse effects

No data available.

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal.

Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process. Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

List of Wastes Code - residues/unused products

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

List of Wastes Code - used product

160306 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; off-specification batches and unused products; organic wastes other than those mentioned in 16 03 05

List of Wastes Code - contaminated packaging

150106 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); mixed packaging

Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

Safety Data Sheet

according to UK REACH Regulation

Page 8 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Inland waterways transport (ADN)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

Refer to section 6 - 8

14.7. Maritime transport in bulk according to IMO instruments

not relevant

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

2010/75/EU (VOC): not determined

2004/42/EC (VOC): not determined

Information according to 2012/18/EU (SEVESO III): Not subject to 2012/18/EU (SEVESO III)

Additional information

Safety Data Sheet according to UK-REACH Regulation

This mixture is classified as not hazardous according to GHS (GB CLP).

UK REACH Appendix XVII, No (mixture): not relevant

National regulatory information

Water hazard class (D): 1 - slightly hazardous to water

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Changes

Rev. 1,0; Initial release 08.05.2018

Rev. 2,0; Revision 03.04.2020 Changes in chapter: 2-16

Rev. 3,0; Revision 02.03.2020 Changes in chapter: 1-16

Safety Data Sheet

according to UK REACH Regulation

Page 9 of 9

Print date: 13.03.2023

Revision date: 02.03.2023

VGI 300

Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

CAS: Chemical Abstracts Service

CLP: Classification, Labeling, Packaging

DNEL: Derived No Effect Level

d: day(s)

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

ECHA: European Chemicals Agency

ECOSAR: Ecological Structure Activity Relationships

EWC: European Waste Catalogue

IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

IUCLID: International Uniform Chemical Information Database

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany)

OECD: Organisation for Economic Co-operation and Development

PNEC: Predicted No Effect Concentration

PBT: Persistent, bio-cumulative, toxic

QSAR: Quantitative Structure-Activity Relationship

RID: Regulation Concerning the International Transport of Dangerous Goods by Rail

RTECS: Registry of Toxic Effects of Chemical Substances

SVHC: Substance of Very High Concern

TRGS: Technische Regeln für Gefahrstoffe

UN: United Nations

vPvB: very persistent and very bio-cumulative

VOC: Volatile Organic Compounds

w: week(s)

None listed.

Further Information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)