meusburger

M-LINE MICRO MOTOR HANDPIECE, LONG

PRODUCT DESCRIPTION

- » Long and slim tool holder for demanding work, even in hard-to-reach areas
- » Efficient tool change due to keyless quick clamping system with high clamping force
- » Smooth operation even at highest speeds
- » Ergonomic aluminium housing with built-in front fan against dirt and dust
- » Integrated motor cooling for longest switch-on and service life
- » Illuminated on/off switch conveniently located on the handpiece

INCLUDED IN THE DELIVERY


- » Ø3 mm collet for quick-action clamping chuck (GESM 20015) with slotted spring pin
- » Collet wrench (20016) and locking wrench (GESM 20017)
- » Motor cable

Wt.	d1	Ik ¹⁾	Output	n	No.	EUR
346 g	3	1.85 m	260 W	1,000 - 50,000 min ⁻¹	GESM 2008/260/50	< >
1) lk: cable length						

Spare parts and repair by request

CHARACTERISTICS

GESM 2008	Value		
Motor type	Brushless DC motor		
Torque	8.9 Ncm		
Concentricity	< 0,02 mm		



GESM 2008