meusburger

MATERIAL NO.:	1.2311						
DESIGNATION: DIN: AFNOR: UNI: AISI:	40 CrMnMo 7 40 CMD 8 35 CrMo 8 KU P20 C 0.40 Si 0.40 Mn 1.50 Cr 1.90 Mo 0.20			TECHNICAL TIP: >>> The core strength decreases with increasing plate thickness: for thickness > 300 we recommend 1.2738.			
INDICATORY ANALYSIS:							
STRENGTH:	280 - 325 HB (≈ 950 - 1100 N/mm²)						
THERMAL CONDUCTIVITY AT 100°C:	35 W m K						
COEFFICIENT OF THERMAL EXPANSION [10°/K]	100°C 12.0	200°C 12.8	300°C 13.3	400°C 13.5	500°C	600°C	700°(
CHARACTER:	» Alloyed and pre-toughened tool steel, especially suitable for polishing; high dimensional stability						
APPLICATION:	>> Cavity plates, inserts and high-tensile machine parts						
HEAT TREATMENT:	good suitability for polishing; for higher surface requirements we recommend stee for through hardening >>> Etching, EDM: possible >>> Nitriding: increases the steel's wear resistance >>> Hard chrome plating: particularly increases the steel's wear resistance and corrosion resistance Already pre-toughened; usually no heat treatment required						nend stee
	 Soft annealing: 720 to 740°C for about 2 to 4 hours slow controlled cooling inside the furnace Nitriding: before nitriding, stress-relieving heat treatment at 580°C (Meusburger standard) is recommended. Hardening: 840 to 860°C quenching in oil/hot bath (180 to 220°C) obtainable hardness: 52 HRC Tempering: slow heating to tempering temperature immediately after hardening; 						

TEMPERING CHART:

