



PRECISION VICE HWS 510

## **PRODUCT DESCRIPTION**

» For horizontal, vertical and lateral milling, grinding, inspection and EDM work



- » Pull-down effect prevents lifting of the workpiece
- » Angle accuracy and parallelism of 0.003/100 mm
- » Actuation via hexagon key and quick adjustment via stub shaft





## **MATERIAL**

» Hardened steel, 60 HRC

## **INCLUDED IN THE DELIVERY**

» Includes clamping claws, clamping key, adjustable and fixed stops

Wt.	h	h1	I	I1	<b>SK</b> <sup>1)</sup>	b	No.	EUR
2.8 kg	56	28	175	80	5	60	HWS 510/ 60	<>
5.8 kg	75	40	220	100	10	75	HWS 510/ 75	<>
10.9 kg	87	45	260	120	15	100	HWS 510/100	<>
19.8 kg	100	50	330	160	20	125	HWS 510/125	<>

<sup>1)</sup> SK: clamping force [kN]