

Safety Data Sheet

according to UK REACH Regulation

Page 1 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

V 76925

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Polishing agent

Uses advised against

Any non-intended use.

1.3. Details of the supplier of the safety data sheet

Company name:	Meusburger Georg GmbH & Co KG	
Street:	Kesselstrasse 42	
Place:	A-6960 Wolfurt	
Telephone:	+43 5574 6706-0	Telefax: +43 5574 6706-12
e-mail:	office@meusburger.com	
Internet:	www.meusburger.com	
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Otto-Hahn-Str. 36 D-48161 Muenster	e-mail: info@tge-consult.de Tel.: +49 2534 41594-0 www.tge-consult.de

1.4. Emergency telephone number:

Poison Information Center Mainz, Germany, Tel: +49(0)6131/19240

Further Information

Safety Data Sheet according to UK-REACH Regulation

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GB CLP Regulation

Asp. Tox. 1; H304

Full text of hazard statements: see SECTION 16.

2.2. Label elements

GB CLP Regulation

Hazard components for labelling

Kerosine (petroleum); Straight run kerosine

Signal word: Danger

Pictograms:



Hazard statements

H304 May be fatal if swallowed and enters airways.

Precautionary statements

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/doctor.

Safety Data Sheet

according to UK REACH Regulation

Page 2 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

P331	Do NOT induce vomiting.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.

2.3. Other hazards

The substances in the mixture (> 0.1%) do not meet the PBT/vPvB criteria according to UK REACH.
This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

CAS No	Chemical name	Quantity
EC No	GHS Classification	
REACH No		
Index No		
8008-20-6	Kerosine (petroleum); Straight run kerosine	15 - 20 %
232-366-4	Asp. Tox. 1; H304	
649-404-00-4		

Full text of H and EUH statements: see section 16.

Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
		Specific Conc. Limits, M-factors and ATE	
8008-20-6	232-366-4	Kerosine (petroleum); Straight run kerosine	15 - 20 %
		inhalation: LC50 = (>5,28) mg/l (vapours); dermal: LD50 = >2000 mg/kg; oral: LD50 = >5000 mg/kg	

Further Information

Product does not contain listed SVHC substances > 0.1 % according to UK REACH.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After inhalation

In case of accident by inhalation: remove casualty to fresh air and keep at rest. In case of respiratory tract irritation, consult a physician.

After contact with skin

Gently wash with plenty of soap and water. In case of skin irritation, seek medical treatment.

After contact with eyes

Rinse cautiously with water for several minutes. In case of troubles or persistent symptoms, consult an

Safety Data Sheet

according to UK REACH Regulation

Page 3 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

ophthalmologist.

After ingestion

Rinse mouth thoroughly with water. Let water be drunken in little sips (dilution effect). Do NOT induce vomiting.
In all cases of doubt, or when symptoms persist, seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂). Dry extinguishing powder. Alcohol resistant foam. Atomized water.

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Carbon monoxide. Carbon dioxide (CO₂).

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.
Co-ordinate fire-fighting measures to the fire surroundings.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Safe handling: see section 7

For non-emergency personnel

Wear personal protection equipment (refer to section 8).

For emergency responders

No special measures are necessary.

6.2. Environmental precautions

Discharge into the environment must be avoided.

6.3. Methods and material for containment and cleaning up

For containment

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents).
Treat the recovered material as prescribed in the section on waste disposal.

For cleaning up

Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

SECTION 7: Handling and storage

Safety Data Sheet

according to UK REACH Regulation

Page 4 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

7.1. Precautions for safe handling

Advice on safe handling

Wear suitable protective clothing. See section 8.

Advice on protection against fire and explosion

Usual measures for fire prevention.

Advice on general occupational hygiene

Always close containers tightly after the removal of product. Do not eat, drink, smoke or sneeze at the workplace. Wash hands before breaks and after work.

Further information on handling

General protection and hygiene measures: See section 8.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place.

Hints on joint storage

Do not store together with: Explosives. Oxidizing solids. Oxidizing liquids. Radioactive substances. Infectious substances. Food and animal feedingstuff.

Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorption of humidity.

Recommended storage temperature: 20 °C

Protect against: frost. UV-radiation/sunlight. heat. Humidity

7.3. Specific end use(s)

See section 1.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Additional advice on limit values

To date, no national critical limit values exist.

8.2. Exposure controls



Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment.

Provide adequate ventilation.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear safety glasses; chemical goggles (if splashing is possible). BS/EN 166

Hand protection

Wear suitable gloves.

Suitable material:

FKM (fluororubber). - Thickness of glove material: 0,4 mm

Safety Data Sheet

according to UK REACH Regulation

Page 5 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

Breakthrough time \geq 8 h
 Butyl rubber. - Thickness of glove material: 0,5 mm
 Breakthrough time \geq 8 h
 CR (polychloroprenes, Chloroprene rubber). - Thickness of glove material: 0,5 mm
 Breakthrough time \geq 8 h
 NBR (Nitrile rubber). - Thickness of glove material: 0,35 mm
 Breakthrough time \geq 8 h
 PVC (Polyvinyl chloride). - Thickness of glove material: 0,5 mm
 Breakthrough time \geq 8 h

For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

The selected protective gloves have to satisfy the specifications of the Personal Protective Equipment at Work (Amendment) Regulations 2022 and the standard EN ISO 374.

Check leak tightness/impermeability prior to use. In the case of wanting to use the gloves again, clean them before taking off and air them well.

Skin protection

Suitable protective clothing: Lab apron.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500 (D).

Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required.

Respiratory protection necessary at:

- Exceeding exposure limit values
- Insufficient ventilation and aerosol or mist formation

Suitable respiratory protective equipment: particulates filter device (DIN EN 143). Type: P1-3

The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

Environmental exposure controls

Do not allow uncontrolled discharge of product into the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Paste
Colour:	grey
Odour:	characteristic
Odour threshold:	not determined

	Test method
Melting point/freezing point:	$<0\text{ }^{\circ}\text{C}$
Boiling point or initial boiling point and boiling range:	$>100\text{ }^{\circ}\text{C}$
Flammability:	not determined
Lower explosion limits:	not determined
Upper explosion limits:	not determined
Flash point:	$>100\text{ }^{\circ}\text{C}$ DIN 51758
Auto-ignition temperature:	not determined
Decomposition temperature:	not determined
pH-Value:	8,5 DIN 53785

Safety Data Sheet

according to UK REACH Regulation

Page 6 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

Viscosity / kinematic:	not determined
Water solubility:	not determined
Solubility in other solvents	
not determined	
Dissolution rate:	not relevant
Partition coefficient n-octanol/water:	SECTION 12: Ecological information
Dispersion stability:	not relevant
Vapour pressure:	not determined
Density:	1,23 g/cm ³ DIN 51757
Bulk density:	not determined
Relative vapour density:	not determined
Particle characteristics:	not relevant

9.2. Other information

Information with regard to physical hazard classes

Explosive properties	
none	
Sustaining combustion:	Not sustaining combustion
Self-ignition temperature	
Solid:	not relevant
Gas:	not relevant
Oxidizing properties	
none	

Other safety characteristics

Evaporation rate:	not determined
Solvent separation test:	not determined
Solvent content:	not determined
Solid content:	not determined
Sublimation point:	not determined
Softening point:	not determined
Pour point:	not determined
Viscosity / dynamic:	not determined
Flow time:	not determined

Further Information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

Refer to chapter 10.5.

10.4. Conditions to avoid

Protect against: UV-radiation/sunlight. heat.

10.5. Incompatible materials

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong.

Safety Data Sheet

according to UK REACH Regulation

Page 7 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

10.6. Hazardous decomposition products

Does not decompose when used for intended uses.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in GB CLP Regulation

Toxicokinetics, metabolism and distribution

No data available.

Acute toxicity

Based on available data, the classification criteria are not met.

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
8008-20-6	Kerosine (petroleum); Straight run kerosine				
	oral	LD50 >5000 mg/kg	Rat	ECHA dossier	OECD 420
	dermal	LD50 >2000 mg/kg	Rat	ECHA dossier	OECD 402
	inhalation (4 h) vapour	LC50 (>5,28) mg/l	Rat	ECHA dossier	OECD 403

Irritation and corrosivity

Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

May be fatal if swallowed and enters airways.

Specific effects in experiment on an animal

No data available.

11.2. Information on other hazards

Endocrine disrupting properties

This product does not contain a substance (> 0.1 %) that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

Other information

No data available.

SECTION 12: Ecological information

12.1. Toxicity

The product has not been tested.

CAS No	Chemical name

Safety Data Sheet

according to UK REACH Regulation

Page 8 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

	Aquatic toxicity	Dose		[h] [d]	Species	Source	Method
8008-20-6	Kerosine (petroleum); Straight run kerosine						
	Acute fish toxicity	LC50 5 mg/l	LL50: 2-	96 h	Oncorhynchus mykiss	ECHA dossier	OECD 203
	Acute algae toxicity	ErC50 3 mg/l	EL50: 1-	72 h	Pseudokirchnerella subcapitata	ECHA dossier	OECD 201
	Acute crustacea toxicity	EC50 1,4 mg/l	EL50:	48 h	Daphnia magna	ECHA dossier	OECD 202

12.2. Persistence and degradability

The product has not been tested.

CAS No	Chemical name			
	Method	Value	d	Source
	Evaluation			
8008-20-6	Kerosine (petroleum); Straight run kerosine			
	OECD 301F / ISO 9408 / EEC 92/69 annex V, C.4-D	58,6%	28	ECHA dossier
	Moderately/partially biodegradable			

12.3. Bioaccumulative potential

No indication of bioaccumulation potential.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

The aforementioned statement applies to substances contained in the product with a minimum content of 0.1 %.

12.7. Other adverse effects

No data available.

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Observe in addition any national regulations! Consult the local waste disposal expert about waste disposal.

Non-contaminated packages may be recycled.

According to (EWC) European Waste Catalogue, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process.

Control report for waste code/ waste marking according to (EWC) European Waste Catalogue:

List of Wastes Code - residues/unused products

Safety Data Sheet

according to UK REACH Regulation

Page 9 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

070604 WASTES FROM ORGANIC CHEMICAL PROCESSES; wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics; other organic solvents, washing liquids and mother liquors; hazardous waste

List of Wastes Code - used product

070604 WASTES FROM ORGANIC CHEMICAL PROCESSES; wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics; other organic solvents, washing liquids and mother liquors; hazardous waste

List of Wastes Code - contaminated packaging

150110 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); packaging containing residues of or contaminated by hazardous substances; hazardous waste

Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

Inland waterways transport (ADN)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

Refer to section 6 - 8

14.7. Maritime transport in bulk according to IMO instruments

not relevant

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Safety Data Sheet

according to UK REACH Regulation

Page 10 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

EU regulatory information

2010/75/EU (VOC):	=< 20% (calculated)
2004/42/EC (VOC):	=< 200 g/l (calculated)
Information according to 2012/18/EU (SEVESO III):	Not subject to 2012/18/EU (SEVESO III)

Additional information

Safety Data Sheet according to UK-REACH Regulation
 The mixture is classified as hazardous according to GHS (GB CLP).
 UK REACH Appendix XVII, No (mixture): 3

National regulatory information

Employment restrictions:	Observe restrictions to employment for juveniles according to the 'juvenile work protection guideline' (94/33/EC).
Water hazard class (D):	2 - obviously hazardous to water

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Changes

Rev. 1,0; Initial release: 20.04.2018
 Rev. 2.0; Revision 01.04.2020, Changes in chapter: 2-16
 Rev. 3.0; Revision 15.02.2023, Changes in chapter: 1-16

Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 AGW: Arbeitsplatzgrenzwert
 CAS: Chemical Abstracts Service
 CLP: Classification, Labelling and Packaging of substances and mixtures
 DNEL: Derived No Effect Level
 d: day(s)
 EINECS: European Inventory of Existing Commercial chemical Substances
 ELINCS: European List of Notified Chemical Substances
 ECHA: European Chemicals Agency
 EWC: European Waste Catalogue
 IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)
 ICAO: International Civil Aviation Organization
 ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)
 GHS: Globally Harmonized System of Classification and Labelling of Chemicals
 GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany)
 h: hour
 LOAEL: Lowest observed adverse effect level
 LOAEC: Lowest observed adverse effect concentration
 LC50: Lethal concentration, 50 percent
 LD50: Lethal dose, 50 percent
 NOAEL: No observed adverse effect level

Safety Data Sheet

according to UK REACH Regulation

Page 11 of 11

Print date: 13.03.2023

Revision date: 15.02.2023

V 76925

NOAEC: No observed adverse effect concentration
 NLP: No-Longer Polymers
 N/A: not applicable
 OECD: Organisation for Economic Co-operation and Development
 PNEC: predicted no effect concentration
 PBT: Persistent bioaccumulative toxic
 RID: Regulation Concerning the International Transport of Dangerous Goods by Rail
 REACH: Registration, Evaluation, Authorisation of Chemicals
 SVHC: substance of very high concern
 TRGS: Technische Regeln für Gefahrstoffe
 UN: United Nations
 VOC: Volatile Organic Compounds

Classification for mixtures and used evaluation method according to GB CLP Regulation

Classification	Classification procedure
Asp. Tox. 1; H304	Calculation method

Relevant H and EUH statements (number and full text)

H304 May be fatal if swallowed and enters airways.

Further Information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)